







8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852450-1		A	122500-1	LEADMAKER	POST FEED	CUTS CARRIER	
1852450-2		A	565435-5	BENCH MODEL K	PRE FEED	CUTS CARRIER	
1852450-3		A	354500-1	BENCH MODEL G	PRE FEED	CUTS CARRIER	
1852450-6		A	122500-1	LEADMAKER	POST FEED	CONTINUOUS CARRIER	
7-1852450-7		A	-	-	-	SPARE PARTS	

- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- △ APPLY TORQ-SEAL IN ALLEN SOCKET TO FILL HOLE AFTER FLAT HD HAS BEEN ADJUSTED TO CORRECT HEIGHT AT QUALIFICATION. APPLY PN 1-23419-5 LOC-TITE TO THREADS.
- △ THIS APPLICATOR APPLIES A TERMINAL W/A SEAL



TERMINAL NAME: TERMINAL, MALE, 1.5 SYSTEM (SEALED)					
TYCO PN	MANUF PN	YAZAKI TERMINAL - YAZAKI CRIMP SPECS			
1832587	7114-4103-08				
-	-	PAD LTR	CRIMP HEIGHT	WIRE SIZE	
-	-	A	1.25±0.05mm [.049±.002]	16AWG or 1.25mm2	
-	-	B	1.25±0.05mm [.049±.002]	1mm2	
-	-	C	1.20±0.05mm [.047±.002]	18AWG or 0.85mm2	
-	-	D	-	-	
SEAL PN	-	CRIMP	SIZE	TYPE	RANGE
286814-1	7158-3031-90	WIRE	2.18mm [.086]	F	0.85-1.25mm2
-	-	INSUL	3.45mm [1.36]	O	Ø1.63-2.40mm
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPLICATOR INSTRUCTIONS		SET UP GAGE
4.98-5.36	114-1056	11.05	408-8040		458637-1



-	2	2	2	2	-	3-354779-5	PIN, WIRE DISC, .3165	128
-	2	2	2	2	-	3-354779-0	PIN, WIRE DISC, .3140	127
-	2	2	2	2	-	3-354779-2	PIN, WIRE DISC, .3150	126
-	-	-	REF	-	..	455749-1	GUARD WINDOW	116
-	-	REF	-	-	..	679532-1	INSERT, GUARD	115
-	1	1	1	1	-	690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
-	1	1	1	1	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
-	1	1	1	1	-	318563-1	GUARD, FRONT CHIP	89
-	1	1	1	1	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	1	-	217238-1	GENERAL INSTRUCTION PKG	71
-	1	1	1	1	-	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	-	21017-2	SCREW, DRIVE	66
-	1	1	1	1	-	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	1	1	1	1	-	23030-1	SCR, SKT HD CAP 6-32 x .25	62
-	1	1	1	1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	1	-	1-21003-9	SCR, FLT SKT HD CAP 6-32 X .375	57
-	1	1	1	1	-	458537-2	PAWL, FEED	56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
-	2	2	2	2	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	53
-	1	1	1	1	-	21018-5	NUT, HEX, REG 6-32	52
-	1	1	1	1	-	811242-2	BUMPER, HOLD DOWN	51
-	1	1	1	1	-	690753-1	SPACER, TONKER	50
-	-	1	-	-	..	690602-6	CAM, PRE FEED, 1 5/8	49
-	-	-	1	-	..	690602-5	CAM, PRE FEED, 1 1/8	48
-	1	-	-	1	-	690501-4	CAM, POST FEED, 1 5/8	47
-	1	1	1	1	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MOCA)	46
-	1	1	1	1	-	690191-1	PLUG, NYLON	45
-	1	1	1	1	-	455673-1	RAM, SIDE FEED	44
-	1	1	1	1	-	690125-1	SHIM SUB-ASSY	43
-	1	1	1	1	-	690124-1	WASHER, RAM (.115)	42
-	1	1	1	1	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	1	-	23241-6	BALL, STEEL	40
-	1	1	1	1	-	690170-1	SPRING, COMPRESSION	39
-	1	1	1	1	-	1-690142-0	DISC, INSULATION	38
-	1	1	1	1	-	354777-1	WIRE DISC, ASSEMBLY	37
-	1	1	1	1	-	22480-5	SPRING, COMPRESSION	36
-	1	1	1	1	-	690212-1	POST, RAM	35
-	1	1	1	1	-	690786-3	TERMINAL SUPPORT	34
-	2	2	2	2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	1	1	1	1	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	1	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	1	-	1320908-8	SPACER, STRIP GUIDE	30
-	1	1	1	1	-	1633091-5	ASSEMBLY, STRIP GUIDE	29
-	1	1	1	1	-	1-455888-0	SPACER, CRIMPER	28
-	1	1	1	1	-	1320928-1	PLATE, STRIP GUIDE	24
-	1	-	-	1	-	690472-2	STRIPPER	22
-	1	1	1	1	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	1	1	-	-	691353-1	STRIPPER	19
-	1	-	-	-	-	679625-2	SHEAR HOLDER, FRONT (NO CUT)	17
-	1	1	1	1	-	3-22280-3	SPRING, COMPRESSION	12
-	1	1	1	1	-	690461-2	STOP, SHEAR	11
-	-	1	1	1	-	1-690459-0	SHEAR HOLDER, FRONT	10
-	1	1	1	1	-	318707-2	FLOATING SHEAR, FRONT	9
1	1	1	1	1	-	1633535-8	ANVIL, COMBINATION	8
-	1	1	1	1	-	318701-1	DEPRESSOR, SHEAR	5
-	1	1	1	1	-	2-238011-2	BLOCK, CRIMPER SPACER	4
1	1	1	1	1	-	8-1583690-9	CRIMPER, INSUL O	3
-	1	1	1	1	-	1-455888-5	SPACER, CRIMPER	2
1	1	1	1	1	-	8-1633305-3	CRIMPER, WIRE PREMIUM	1

-77 -6 -3 -2 -1 U/M				PART NO		DESCRIPTION				ITEM NO								
THIS DRAWING IS A UNPUBLISHED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO THE TYCO ELECTRONICS CORPORATION'S POLICY AND REVISIONS SHOULD BE CONTACTED FOR THE LATEST REVISION.						DWN	16MAR2007	 Tyco Electronics Harrisburg, PA 17105-3608										
						M. HERR												
						CHK	16MAR2007											
						G. BAILEY												
						APVD	16MAR2007											
						T. BENCHOFF												
DIMENSIONS:						TOLERANCES UNLESS OTHERWISE SPECIFIED:					NAME							
INCHES																		
						0 PLC	±											
						1 PLC	±0.1											
						2 PLC	±0.01											
						3 PLC	±0.001											
						4 PLC	±0.0001											
						ANGLES												
MATERIAL						FINISH			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
-						-			A1	00779	C=1852450	-						
CUSTOMER DRAWING											SCALE	3:5	SHEET	1	OF	1	REV	A

CUSTOMER VIEWABLE ASSEMBLY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852450-2](#)