

Bosch GST135BCE jigsaw with bosch precision control , complete with saw blades, dust extraction set and carrying case



FEATURES:

- At the press of a button the "Precision Control" guide jaw adjusts itself automatically to the varying saw blade thicknesses for precise angle cuts and guidance
- Highest possible convenience with Bosch "SDS", the world's easiest way to change saw blades - using only one hand
- Constant sawing progress even under load due to Constant Electronic
- Accelerator function for sensitive sawing
- Exemplary running smoothness when sawing which ensures best results as well as low-fatigue working
- When working under extreme conditions its lifetime is up to five times that of conventional tools
- Thanks to electronics with speed control, it has 25% more torque than the legendary Bosch GST 85 Professional
- The sole plate can be adjusted without tools (+/- 45° as well as 15 mm forwards/backwards)
- Easy to service thanks to the uncomplicated changing of the cable and carbon brushes
- Sturdy aluminium sole plate with steel reinforcement, also ideal for metalworking
- Sawdust blower allows for a clear view, can be switched-off for effective dust extraction
- 4-level pendulum action for tear-free cuts up to aggressive cuts

COMES WITH:

- Carrying case

- 3 saw blades, 1 splinter guard
- Dust extraction set

PRODUCT SPECIFICATION

TECHNICAL DATA:

- Barcode: 3165140307369
- Rated power input: 720 W
- No-load stroke rate: 500 – 2.800 rpm
- Weight: 2,70 kg
- Cable length: 4 M
- Stroke height: 26,0 mm

CUTTING DEPTH:

- Barcode: 3165140307369
- Cutting depth in wood: 135 mm
- Cutting depth in aluminium: 20 mm
- Cutting depth in unalloyed steel: 10 mm
- Total Shipping Weight: 4kg