


Adhesive Lined Grommet Edging

Grommet edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. In addition to standard grommet edging, Panduit offers grommet edging with a pressure sensitive adhesive that lines the base of the product. This provides for an easy, clean, and secure application. Adhesive lined grommet edging is available in natural and weather resistant polyethylene and can be used on straight or irregular shaped surfaces. Adhesive lined grommet edging is a part of the innovative solutions Panduit provides to protect wire and cable to help you manage your physical infrastructure.

To install, clean the edge of the panel, install the product over the edge of the panel, and then apply thumb pressure to activate the adhesive and the installation is complete.



Key Features

Benefits

Polyethylene material	Economical, durable, and highly flexible; weather resistant option available
Adhesive lined	Ensures the product will stay where it is installed; eliminates messy, user supplied adhesives for a faster and cleaner installation
Slotted or solid wall construction	Use on irregularly shaped and round panel holes as well as straight paths to support a range of applications
No liner to remove from adhesive	Increases productivity and lowers installed cost
Available on 100' reels	Allows for easy handling and dispensing of product

Technical Information

Material:	Polyethylene or weather resistant polyethylene with rubber based adhesive; RoHS compliant
Maximum temperature rating:	122°F (50°C)
Minimum temperature rating:	-40°F (-40°C)
Color:	Available in natural or black (0)
Flammability rating:	UL HB


Use these tables as a guide to determine Panduit grommet edging sizes. The most common gauges for electrical applications of sheet metal dimensions are listed based on the Manufacturer Standard Gauge for Steel.

Gauge	Manufacturer Standard Gauge for Steel (In.)
5	.2092
6	.1943
7	.1793
8	.1644
9	.1495
10	.1345
11	.1196
12	.1046
13	.0897


Gauge	Manufacturer Standard Gauge for Steel (In.)
14	.0747
15	.0673
16	.0598
17	.0538
18	.0478
19	.0418
20	.0359
21	.0329
22	.0299

Gauge	Manufacturer Standard Gauge for Steel (In.)
23	.0269
24	.0239
25	.0209
26	.0179
27	.0164
28	.0149
29	.0135
30	.0120

Adhesive Lined Grommet Edging



Style **GEE_F-A-**
Slotted Wall



Style **GES_F-A-**
Solid Wall

Ordering Information

			Panel Thickness		Dimensions A		Dimensions B			Std. Pkg. Qty.*
Part Number**	Material	Color	In.	mm	In.	mm	In.	mm	Feet Per Pkg.	
Slotted Wall										
GEE62F-A-C	Continuous Polyethylene with Adhesive	Natural	.036 – .062	.9 – 1.6	.13	3.3	.16	4.1	100	1
GEE62F-A-C0		Black	.036 – .062	.9 – 1.6	.13	3.3	.16	4.1	100	1
GEE99F-A-C		Natural	.062 – .099	1.6 – 2.5	.17	4.3	.19	4.7	100	1
GEE99F-A-C0		Black	.062 – .099	1.6 – 2.5	.17	4.3	.19	4.7	100	1
GEE144F-A-C		Natural	.099 – .144	2.5 – 3.7	.21	5.4	.22	5.6	100	1
GEE144F-A-C0		Black	.099 – .144	2.5 – 3.7	.21	5.4	.22	5.6	100	1
Solid Wall										
GES62F-A-C	Continuous Polyethylene with Adhesive	Natural	.036 – .062	.9 – 1.6	.13	3.3	.16	4.1	100	1
GES62F-A-C0		Black	.036 – .062	.9 – 1.6	.13	3.3	.16	4.1	100	1
GES99F-A-C		Natural	.062 – .099	1.6 – 2.5	.17	4.3	.19	4.7	100	1
GES99F-A-C0		Black	.062 – .099	1.6 – 2.5	.17	4.3	.19	4.7	100	1
GES144F-A-C		Natural	.099 – .144	2.5 – 3.7	.21	5.4	.22	5.6	100	1
GES144F-A-C0		Black	.099 – .144	2.5 – 3.7	.21	5.4	.22	5.6	100	1


*Order the number of reels required.

**Part numbers with “-C0” are considered weather resistant.


Reel packaging may contain splices.

Other Grommet Edging Products Available Without Adhesive


Nylon
Style **GEE_N-**
Slotted Wall




Polyethylene
Style **GEE_F-**
Slotted Wall
Also available in
Weather Resistant
material




Flame Retardant Polyethylene
Style **GEE_FR-**
Slotted Wall




**Nylon and
Flame Retardant Nylon (-69)**
Style **GE_-**
Slotted Wall



Polyethylene
Style **GES_F-**
Solid Wall
Also available in
Weather Resistant
material



Flame Retardant Polyethylene
Style **GES_FR-**
Solid Wall



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Jalisco, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference WACB16

PANDUIT®

©2010 Panduit Corp.
ALL RIGHTS RESERVED.
Product Bulletin Number **WW-WACB16**
2/2010