




Specifications:

- Maximum cable size: 5.5mm (.216")
- Ratings: 5A at 200Vdc/150 Vac maximum
- Insulation resistance: 100MΩ @ 500Vdc
- Center contact: silver and gold plated brass
- Ground contact: nickel and gold plated brass
- Insulation: noryl SE1
- Cable clamp: silver and gold plated brass
- Spring: nickel and gold plated spring steel
- Cap: nickel and gold plated brass

Mouser Stock No.	Description
174-3300	Nickel plated
174-3301	Nickel plated (black ID ring)
174-3302	Nickel plated (blue ID ring)
174-3305	Nickel plated (red ID ring)
174-3306	Nickel plated (white ID ring)
174-3307	Nickel plated (yellow ID ring)
174-3310	Flash gold plated
174-3311	Flash gold plated (black ID ring)
174-3312	Flash gold plated (blue ID ring)
174-3315	Flash gold plated (red ID ring)
174-3316	Flash gold plated (white ID ring)
174-3317	Flash gold plated (yellow ID ring)
174-3320	Flash gold pin assy/black chrome cap & spring
174-3321	Flash gold pin assy/black chrome cap & spring (black ID ring)
174-3322	Flash gold pin assy/black chrome cap & spring (blue ID ring)
174-3325	Flash gold pin assy/black chrome cap & spring (red ID ring)
174-3326	Flash gold pin assy/black chrome cap & spring (white ID ring)
174-3327	Flash gold pin assy/black chrome cap & spring (yellow ID ring)

Your source for quality electronics. Toll-free full service
(800) 346-6873