



International Components Corporation

Quality Components since 1970

EXTERNAL DRIVE PIEZO ELECTRIC



ROHS COMPLIANT

PART NUMBER:

BRP1407P-20

SPECIFICATIONS:

RATED VOLTAGE:	20 Vp-p
SOUND OUTPUT LEVEL:	80dB @10CM
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	4096 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
ELECTROSTATIC CAPACITY:	10,000 $\pm$ 30%
FRAME DIAMETER:	14.0 mm
FRAME DEPTH:	6.8 mm
MOUNTING DIMENSIONS:	7.6 mm

DIMENSIONS:

