


Coaxial Connectors and Crimping Tools



BNC PC Board/Panel Mount Jacks



Right Angle (Max. Panel Thickness .240") 50 Ohm						EACH		
Stock No.	Mr.'s Type	Mfg. Hgt.	Body	Mounting Posts	Center Contact Plating	1-24	25-99	100-499
512-2171	226990-1	0.625"	Wht. Valox	No	Tin	2.26	2.04	1.70
512-2172	226990-3	0.625"	Wht. Valox	No	Gold	1.94	1.74	1.45
512-2173	227161-1	0.625"	Wht. Valox	Yes	Tin	1.67	1.50	1.25
512-2174	227161-3	0.625"	Wht. Valox	Yes	Gold	1.67	1.50	1.25
512-2176	227161-7	0.519"	Wht. Valox	Yes	Gold	1.67	1.50	1.25
512-2175	226990-2	0.625"	Blk. Valox	No	Tin	1.94	1.74	1.45
512-2178	226990-6	0.625"	Blk. Valox	No	Gold	1.94	1.74	1.45
512-2177	227161-2	0.625"	Blk. Valox	Yes	Tin	1.67	1.50	1.25
512-2180	227161-6	0.625"	Blk. Valox	Yes	Gold	1.88	1.50	1.25
512-2179	227161-9	0.519"	Blk. Valox	Yes	Gold	1.88	1.50	1.25
512-2181	227433-1	0.625"	Metal	No	Tin	4.44	4.00	3.33
512-2182	227676-1	0.625"	Metal	No	Gold	2.31	2.08	1.73
512-2183	227661-1	0.625"	Metal	Yes	Tin	2.25	2.03	1.69
512-2184	227677-1	0.625"	Metal	Yes	Gold	2.25	2.03	1.69

Vertical (Max. Panel Thickness .240") 50 Ohm						1-24	25-99	100-499
512-2185	226993-1	1.375"	Wht. Valox	No	Tin	4.44	4.00	3.33
512-2187	226993-3	1.375"	Wht. Valox	No	Gold	4.44	4.00	3.33
512-2189	227222-1	1.375"	Wht. Valox	Yes	Tin	1.82	1.63	1.36
512-2186	227222-3	1.375"	Wht. Valox	Yes	Gold	1.67	1.50	1.25
512-2193	227222-6	1.375"	Blk. Valox	Yes	Gold	2.13	1.92	1.60
512-2195	227671-1	1.375"	Metal	Yes	Tin	2.13	1.94	1.60
512-2188	227673-1	1.375"	Metal	Yes	Gold	1.92	1.73	1.44

Hardware						1-99	100-499	500-999
Stock No.	Mr.'s Type	Description	EACH					
512-2190	1-329632-2	Lock Washer	.15	.13	.12			
512-2191	1-329631-2	Jam Nut	.17	.15	.14			

Twin BNC Connectors



Plugs — Fig. A								EACH		
Stock No.	Mr.'s Type	For RG/U Cable	Contact Plating	Body Plating	Dielectric	CERTI-CRIMP™ Hand Tool		1-24	25-49	50-99
512-2340	332225	108, 108A	S	S	T	69667		16.48	14.83	12.36
512-2342	332225-5	108, 108A	S	N	PP	69667		13.61	12.38	11.24

Bulkhead Jack — Fig. B								22.17	19.95	16.63
512-2154	332342	108, 108A	S	N	PP	69667				

Right-Angle PC Board/Panel Mount Jacks — Fig. C								6.80	6.12	5.10
Stock No.	Mr.'s Type	Body Material	Mounting Posts	EACH				1-24	25-49	50-99
512-2344	228686-1	Wht. Valox	Yes							

Bulkhead Jack Adapter — Fig. D								20.60	18.54	15.45
Stock No.	Mr.'s Type	Contact Plating	Body Plating	EACH				1-24	25-49	50-99
512-2346	332215	S	N							

50 Ohm N Connectors

MIL-C-39012, Class 11, Category B qualified. Working voltage 1000 volt, RMS at sea level. Frequency Range: 0-11 GHz. Crimp Type: D.



Crimp Plugs											EACH		
Stock No.	Mr.'s Type	For RG/U Cable	Contact Plating	Body Plating	Dielectric	Style	CERTI-CRIMP™ Hand Tool	1-24	25-49	50-99			
512-2236	1-225661-2	58, 58A, 58B, 58C	G	N	T	Mil type	220045-2	10.68	9.51	7.85			
512-2238	225361-1	58, 58A, 58B, 58C	G	S	T	Mil type	220045-2	22.81	20.73	19.01			
512-2241	225661-2	8, 9A, 213	G	N	T	Mil type	220015-1	10.47	9.42	7.85			
512-2242	1-227086-0	8, 8A, 213	G	N	T	Commercial	220015-1	8.12	7.38	6.77			
512-2248	225661-1	9, 9A, 9B, 214	G	N	T	Mil type	220015-1	18.40	16.73	15.33			

Same Day Shipments For Product In Stock

SHV Connectors



Safe-tested at 5000 volts DC. Looks like, but isn't intermateable with other bayonet-type connectors. Comply with Bureau of Standard's specification ND-545. Polarized center contacts that are recessed in the dielectric. Crimp Type: D.

Crimp Plugs								EACH		
Stock No.	Mr.'s Type	For RG/U Cable	Contact Plating	Body Plating	Dielectric	CERTI-CRIMP™ Hand Tool		1-24	25-49	50-99
512-2254	51426-4	58, 58A, 58B, 58C	G	N	T	220022-1		16.50	15.00	13.62
512-2256	51426-2	*	G	S	T	220022-2		19.47	17.52	14.60

*59, 59A, 59B, 62, 62A, 62B, 124, 140, 210 Belden 9291, 9209, 9268.

Bulkhead Solder Jacks								12.60	11.34	9.45
Stock No.	Mr.'s Type	Contact Plating	Body Plating	Dielectric	EACH			1-24	25-49	50-99
512-2260	51494-1	G	S	T						
512-2262	51494-2	G	N	T				9.70	8.73	7.28

Miniature UHF Connectors



Rated for 335 volts rms at sea level .0 to 2.0 GHz frequency range. Crimp Type: D.

Crimp Plug								EACH		
Stock No.	Mr.'s Type	For RG/U Cable	Contact Plating	Body Plating	Dielectric	CERTI-CRIMP™ Hand Tool		1-24	25-99	100-499
512-2264	226600-1	58, 58A, 58B, 58C	T	N	PP	220149-1		.69	.62	.52

Crimp Jack								2.70	2.43	2.03
512-2266	226602-1	58, 58A, 58B, 58C	T	N	PP	220149-1				

CERTI-CRIMP™ Hand Tools



AMP's finest tools. The CERTI-CRIMP™ ratchet is designed to provide a complete crimp cycle.

512-2400.	69140-1.....	EACH	542.64
512-2401.	69141-1.....	EACH	542.64
512-2402.	69245-1.....	EACH	520.88
512-2407.	69477-1.....	EACH	264.33
512-2409.	69477-2.....	EACH	276.05
512-2406.	69478-1.....	EACH	256.63
512-2133.	69667.....	EACH	764.32
512-2408.	220009-1.....	EACH	284.38
512-2415.	220009-5.....	EACH	435.20
512-2414.	220015-1.....	EACH	770.13
512-2131.	220022-2.....	EACH	399.84
512-2410.	220043-1.....	EACH	353.04
512-2126.	220045-2.....	EACH	428.65
512-2418.	220061-1.....	EACH	506.33
512-2416.	220187-1.....	EACH	234.44

PRO-CRIMPER™ II Hand Tools



Inexpensive and features interchangeable dies. Ratchet control for complete crimping cycle. Precision construction of durable high-carbon steel.

Type 58433-1.	For "O" crimp plugs and jacks on RG58, 59, and 62 cables.	EACH	89.61
512-2380.	58433-1.....		
Type 58433-2.	For hex crimp plugs and jacks on RG-58, 59, and 62 cables.	EACH	96.51
512-2381.	58433-2.....		

ALLIED ► 413