

USB to MOTHERBOARD and USB HUBS



Fig.1



Fig.2



Fig.3

USB Motherboard Adapter

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable
45-1422		1	USB Expansion Ports			2 USB (skt) on Brackets/IDC10F

USB 2.0

onlinecomponents.com

Retail Part No.	Bulk Part No.	Figure No.	Description	Length (Feet)	Color	Cable
45-1451		2	USB 2.0 Hub 4 Port			USB-A to USB-B
45-1452		3	USB 2.0 + IEEE-1394, Hub 7 Port			USB-A to USB-B/IEEE-1394 M/M

MONITOR/VIDEO CABLES



Fig.4



Fig.5



Fig.6



Fig.7



Fig.8



Fig.9



Fig.10

Super VGA Cables–Premium

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Ferrite Bead
45-1866		4&5	HD15 (Male)/HD15 (Female)	6	Putty	8 x 24 AWG, 3 Coax x 28 AWG	Yes
45-1880		4&5	HD15 (Male)/HD15 (Female)	10	Putty	8 x 24 AWG, 3 Coax x 28 AWG	Yes
45-1876		4	HD15 (Male)/HD15 (Male)	6	Putty	8 x 24 AWG, 3 Coax x 28 AWG	Yes
45-1870		4	HD15 (Male)/HD15 (Male)	10	Putty	8 x 24 AWG, 3 Coax x 28 AWG	Yes

Super VGA Cables–High Quality

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Ferrite Bead
45-1846		4&5	HD15 (Male)/HD15 (Female)	6	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1838		4&5	HD15 (Male)/HD15 (Female)	10	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1845		4&5	HD15 (Male)/HD15 (Female)	25	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1860		4&5	HD15 (Male)/HD15 (Female)	50	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1836		4	HD15 (Male)/HD15 (Male)	6	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1839		4	HD15 (Male)/HD15 (Male)	10	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1841		4	HD15 (Male)/HD15 (Male)	25	Black	8 x 24 AWG, 3 Coax x 28 AWG	No
45-1850		4	HD15 (Male)/HD15 (Male)	50	Black	8 x 24 AWG, 3 Coax x 28 AWG	No

VGA Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Ferrite Bead
45-435		4&5	HD15 (Male)/HD15 (Female)	6	Putty	14 x 28 AWG	No
64-4016		4&5	HD15 (Male)/HD15 (Female)	10	Putty	14 x 28 AWG	No
45-476		4	HD15 (Male)/HD15 (Male)	6	Putty	14 x 28 AWG	No
64-4014		4	HD15 (Male)/HD15 (Male)	10	Putty	14 x 28 AWG	No

RGB Specialty Monitor Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Ferrite Bead
45-416		7&8	Video 8 (Male)/DB9 (Male)	4	Putty	8 x 28 AWG Stranded	No
45-1505		6	(5) BNC (Male)/(5) BNC (Male)	6	Black	5 x 28 AWG Mini-Coax	No
45-1509		8&6	DB9 (Male)/(4) BNC (Male) (Does not Include yellow wire & connector)	6	Black	4 x 28 AWG Mini-Coax	No
45-1840		4&6	HD15 (Male)/(5) BNC (Male)	6	Putty	5 x 28 AWG Mini-Coax	Yes

EGA Cables

Retail Part No.	Bulk Part No.	Figure No.(s)	Description	Length (Feet)	Color	Cable	Ferrite Bead
45-308		8&9	DB9 (Male)/DB9 (Female)	6	Putty	9c x 28 AWG	No
45-314		8&9	DB9 (Male)/DB9 (Female)	10	Putty	9c x 28 AWG	No
45-315		8	DB9 (Male)/DB9 (Male)	6	Putty	9c x 28 AWG	No
45-316		8	DB9 (Male)/DB9 (Male)	10	Putty	9c x 28 AWG	No
45-318		8&10	DB9 (Male)/DB9 (Female) without Thumb Screws	10	Putty	9c x 28 AWG	No