


3011 Series

Box Header With Ejectors 2.54mm(0.100")



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.

Contacts: Copper Alloy.

Electrical Characteristics:

Current Rating: 2 A.

Dielectric Withstanding Voltage: AC 1000V.

Insulator Resistance: 1000MΩ min.



Contact Resistance: 20mΩ max.

Operating Temperature: -40°C~+105°C.


Features:

- * Choices of Eject lever.
- * Fully shrouded provides ultimate reliability.
- * Black or gray insulator available.
- * Additional plating options available.



Mates with: 1001




Long Lever




Short Lever



Straight Type




Right Angle Type



P.C. Board Layout



Dip Type



Press Fit Type

Position	Dimension			
	A	B	C	D
10	31.88	10.16	21.84	17.96
14	36.96	15.24	26.92	23.04
16	39.50	17.78	29.46	25.58
20	44.58	22.86	34.54	30.66
26	52.20	30.48	42.16	38.28
30	57.28	35.56	47.24	43.36
34	62.36	40.64	52.32	48.44
40	69.98	48.26	59.94	56.06
50	82.68	60.96	72.64	68.76
60	95.38	73.66	85.34	81.46
64	100.46	78.74	90.42	86.54

Ordering information

3011- 64

Series

No. of
Pin Count

G

G: Gold Plated
C: Selective Gold

00

00: G/F

S

S: Straight
R: Right Angle

*SW: Straight Wire Wrap

P

Blank: Dip Type
P: Press Fit Type

B

B: Black
Y: Grey

1

1: With Long Ejectors
2: With Short Ejectors
3: Without Ejectors

A

A: Tray
Package

* Currently only full gold plated Straight wire wrap available and dip length is 15.0mm.