

Ø 9,43" x 3,346"

Ø 239,5 x 85 mm

62GP

ETRI®

AC High Performance Fans




Approvals

CE, NATO codification

Life expectancy

L-10 LIFE AT 40°C:
25 000 hours




AC Motor

Housing material: aluminium
Impeller material: aluminium
Weight: 4,2 kg
Bearing system: ball bearings

Available with:

- Safety switch
- Terminal block
- Plastic impeller (61G series)



Part Number	Nominal voltage	Airflow	Noise level	Nominal speed	Frequency	Phases	Capacitor (not included)	Input power	Nominal Current	Starting Current	Connection type		Operating temperature	
	V	l/s	dB(A)	RPM	Hz		µF	W	mA	mA	Leads	Terminals	Min.°C	Max.°C
62GP016DC13	230	190	67	2930	50	3		46	290	-	X		-10	70
	400	190	67	2930	50	3		46	170	-	X		-10	70
	230	230	72	3450	60	3		61	250	-	X		-10	70
	400	230	72	3450	60	3		61	145	-	X		-10	70
	230	190	67	2930	50	1	3,2	45	280	-	X		-10	70
	400	190	67	2930	50	1	1	45	170	-	X		-10	70
	230	230	72	3450	60	1	3,2	62	280	-	X		-10	70
	400	230	72	3450	60	1	1	62	160	-	X		-10	70

Additional versions:

Salt spray protected - Shock and vibration protected - Marine specifications
Wide temperature range - Other voltages (consult factory)