




FCM3.25-A-L14



- Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

■ Part Number	FCM3.25-A-L14
■ RoHS Compliancy Status	Compliant
■ Part Description	Adhesive Backed Latching Flat Cable Holder
■ Product Type	Mounting Device
■ Material	Nylon 6.6
■ Color	Gray
■ UL Recognized	E136577
■ Length (In.)	7.30
■ Length (mm)	185.4
■ Width (In.)	3.38
■ Width (mm)	85.9
■ Adhesive Type	Rubber Adhesive
■ Cable Width (In.)	3.38
■ Cable Width (mm)	85.9
■ Environment	Indoors
■ Max. Flat Cable Width (In.)	3.25
■ Max. Flat Cable Width (mm)	82.6
■ Max. Static Load (g)	681
■ Max. Static Load (Lbs.)	1.50
■ Mounting Method	Rubber Adhesive
■ Open Length (In.)	7.3
■ Open Length (mm)	185.4
■ Pricing Description	Flat Cable Mount, Adh., 3.25" (82.6mm) W Cable
■ Screw Size	#6 (M3)
■ Screw Size Metric	M3
■ Min. Order UOM	PC
■ Min. Order Qty.	50

Technical drawing of a metal component, likely a bearing or bushing, showing dimensions in millimeters (mm) and inches (in).

Top View:

- Overall length: 7.30 (185.4)
- Overall width: 1.00 (25.4)
- Central bore diameter: 0.340 (8.64) DIA. C'BORE
- Two side holes: .14 (3.5) DIA. THRU X .17 (4.3) DP., 2 HOLES
- Distance from center bore to side holes: 1.50 (38.1)
- Distance between side holes: 0.94 (23.9)
- Distance from side holes to outer edge: 0.50 (12.7)

Side View:

- Overall height: 0.17 (4.3) MAXIMUM STACKING HEIGHT
- Distance from center bore to side holes: 3.23 (82.0)
- Distance between side holes: 3.38 (85.9)
- Feature labeled: TEAR-TA

PANDUIT PART No.	REC'M. SCREW FASTENER	WEIGHT LBS./100 (g)/PCS.
FCM3.25-A	N/A	3.26 (1480)
FCM3.25-S6	#6 (M3) FL. HD. OR BUTTON HD.	3.04 (1380)

NO WARRANTY EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

ADHESIVE TAPE: PRESSURE SENSITIVE FOAM .040 (1.02) THICK
WITH RUBBER ADHESIVE AND PROTECTIVE LINER. MOUNT
IS DESIGNED TO SUPPORT 1.5 lbs. (680g) MAXIMUM WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

SCALE: 3/4

$$\frac{0.60}{(15.2)^{-}}$$

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER; b) PLACE IN DESIRED LOCATION; c) APPLY PRESSURE TO TOP OF MOUNT.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G00239JE_PB_FCM3.25_00

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

3.25 INCH FLAT CABLE MOUNT
FCM3.25

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± N/A (.XXX) ± N/A
(.XX) ± .020 (.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LGG

	MAT'L:
--	--------

	SCALE
--	--------------

FULL

DATE	7/18/02
------	---------

NYLON 6/6

DRAWING NO.

GB0239JE

DWG
A
SIZE

R	7-18-02	LGG		INITIAL RELEASE-REPLACED G-00173	GB0239JE	1				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		