





REV.	DATE	DESCRIPTION
NC	02/18/03	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



9					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex BNC CRIMP PLUG (RG-58/U PLENUM CABLE)									
8						DRAWN	G.R.S.	01/06/03											
7						CHECKED													
6						ISSUED													
5										PART DESCRIPTION									
4	FERRULE	BRASS	NICKEL	1							BNC CRIMP PLUG (RG-58/U PLENUM CABLE)								
3	CONTACT PIN	BRASS	GOLD	1							PART NO.								
2	INSULATOR	DELRIN	NATURAL	1							112128								
1	BODY	BRASS	NICKEL	1				SHEET	1 OF 1										
	DESCRIPTION	MATERIAL	FINISH	QTY				CAD FILE	C:/112/112128.DWG		DWG. NO.	112128.DWG		REV.	C	SIZE	A	SCALE	NA