








Copyright FCI.



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.PA00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.PA00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.PA00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.PA00

Protection: 4 --> 200 mating
6 --> 500 mating

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.PA00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.PA00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.PA00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.PA00LF

Protection: 4 --> 200 mating
6 --> 500 mating

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection mm	size A3 Scale 2
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	LELEON	1992/09/15	ANGULAR	LINEAR	0.X	±0.1
Eng	PESSON	1992/09/15			0.XX	±0.1
Chr	NIRMAL G	2010-12-06	0.XX*	±2*	0.XXX	±0.1
Appr	SUDHIR V	2010-12-06	Product family			ECN I10-0235
			D-SUB			Spec ref -
			title FEMALE CONNECTOR STD EUROPE straight solder type for PCB 2.40mm			Rev. F
			dwg no C01-8646-0120			
			catalog no -			
			CUSTOMER			sheet 1 of 2

rev	ecn no	dr	date
C	-	JOU	1996/03/01
D	LS05-001	MPE	2005/03/12
E	LS06-0095	LGO	2006/06/19
F	I10-0235	NG	2010-12-06
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17



Copyright FCI.

A

B

C





D

A


B

C

D



PC card drilling dimensions
(after plating – thickness: 1.60 mm)



TIN LEAD PART NUMBER

LEAD FREE PART NUMBER


Part number	D50S24B*PA00	D50S24B*PA00LF
-------------	--------------	----------------

Protection: 4 --> 200 mating
6 --> 500 mating

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED							size A3		Scale 2		
Dr	LELEON	1992/09/15	ANGULAR	LINEAR	0.X	±0.1					
Eng	PESSON	1992/09/15			0.XX	±0.1					
Chr	NIRMAL G	2010-12-06	0.XX* ±2*		0.XXX	±0.1	ECN		I10-0235		
Appr	SUDHIR V	2010-12-06	Product family				D-SUB	Spec ref -			
			title FEMALE CONNECTOR STD EUROPE straight solder type for PCB 2.40mm				dwg no C01-8646-0120				Rev. F
catalog no			-				CUSTOMER		sheet 2 of 2		

REV F - 2006-04-17

PDM: Rev:F

STATUS: Released

Printed: Jan 18, 2011