

Power terminal blocks

Type I

DIN 1 - DIN 3




Rail		35 x 7,5 x 1	PR3.Z2	1SNA 174 300 R1700
Rail		35 x 15 x 2,3	PR4	1SNA 168 500 R1200
Rail		35 x 15 x 1,5	PR5	1SNA 168 700 R2200
Rail		32 x 15 x 1,5	PR1.Z2	1SNA 163 050 R0400

Other end stops, rails and accessories : see section on accessories.

Notes

Accessories



- 1 End stop
(other end stops : see accessories)
- 2 Partition for cover
- 3 Protective cover
(marked cut)
- 4 Protective cover




R See section on markers
Marking method

M 70/31.FF

Spacing 31 mm (1.22")

END OF SERIES



2 studs M8 linked by
1 removable bar 20 x 5 mm

Color	Type	Part numbers
Grey		M 70/31.FF 1SNA 115 143 R1200
Beige V0		M 70/31.FF.V0 1SNA 195 143 R1300

FEC: 4278197

Characteristics

Wire size	DIN	NFC	UL	CSA
Lug	2,5-70 mm²	6-70 mm²	4-00 AWG	0 AWG max.
Bar		20 x 5 mm	.78" x .20"	
Wire-clamp				
Voltage	IEC	IEC		
V~ Without partition	1000-1200	1000	600	600
V~ With partition	1000-1200	1000	600	600
Pulse	8 kV	8 kV		
Pollution degree	3	3		
Current	DIN	NFC		
Rated	178 A	150 A	175 A	200 A
Wire size	DIN	NFC	UL	CSA
Rated / Gauge	50 mm²	50 mm²	2/0 AWG	0 AWG
Lug	Central bolt	Wire clamp	Wire stripping length	
H 13 mm				
6 Nm 52 lb.in				


Type	Part numbers
BAEH	th. 12 mm 1SNA 116 934 R0400
BADH	th. 12 mm 1SNA 116 900 R2700
BAMH	th. 9,1 mm 1SNA 114 836 R0000
ECP31	1SNA 113 690 R2100
CPP311	1 block 1SNA 168 204 R1500
CPP312	2 blocks 1SNA 168 203 R1400
CPP313	3 blocks 1SNA 163 409 R0600
CPU31	1SNA 114 996 R0100

(15) for ECP (6) for CPU

M 120/35.FF

Spacing 35 mm (1.38")

END OF SERIES



2 studs M8 linked by
1 removable bar 25 x 5 mm

Color	Type	Part numbers
Grey		M 120/35.FF 1SNA 115 146 R1500
Beige V0		M 120/35.FF 1SNA 115 146 R1500

FEC: 4278203

Characteristics

Wire size	DIN	NFC	UL	CSA
Lug	2,5-70 mm²	6-95 mm²	2-250 MCM	000 AWG max.
Bar		25 x 5 mm	1" x .20"	
Wire-clamp				
Voltage	IEC	IEC		
V~ Without partition	1000-1200	1000	600	600
V~ With partition	1000-1200	1000	600	600
Pulse	8 kV	8 kV		
Pollution degree	3	3		
Current	DIN	NFC		
Rated	220 A	192 A	255 A	270 A
Wire size	DIN	NFC	UL	CSA
Rated/gauge	70 mm²	70 mm²	250 MCM	000 AWG
Lug	Central bolt	Wire clamp	Wire stripping length	
H 13 mm				
6 Nm 52 lb.in				

Type	Part numbers
BAEH	th. 12 mm 1SNA 116 934 R0400
BADH	th. 12 mm 1SNA 116 900 R2700
BAMH	th. 9,1 mm 1SNA 114 836 R0000
ECP35	1SNA 113 691 R1600
CPP351	1 block 1SNA 168 206 R1700
CPP352	2 blocks 1SNA 168 205 R1600
CPP353	3 blocks 1SNA 163 418 R2600
CPU35	1SNA 116 514 R0700

(15) for ECP (6) for CPU