

Non EMC DIN-Based VectorPak™ Subracks




Front Panels


Screw-mounted front panel kits include handle and identification panel. Available in 3U, 6U and 9U heights and in two widths: 4HP (0.788") and 8HP (1.588"). All mounting hardware, including board mounting support bracket and hardware also included. Brushed aluminum panel with clear irridite plating matches standard finish for Vector packaging products. FPE04-6U panel will have extra center mounting holes for optional 'L' brackets. For no center holes order FPE04-6UB.

Part # Ejector	Part # Fixed	Ht.	HP	A	B
FPE04-3U	FP04-3U	3U	4HP	5.06" (129mm)	0.788" (20mm)
FPE08-3U	FP08-3U	3U	8HP	5.06" (129mm)	1.588" (40mm)
FPE03-6U	FP03-6U	6U	3HP	10.31" (262mm)	0.580" (14mm)
FPE04-6U	FP04-6U	6U	4HP	10.31" (262mm)	0.788" (20mm)
FPE08-6U	FP08-6U	6U	8HP	10.31" (262mm)	1.588" (40mm)


6U FRONT PANEL ASSEMBLY (WITH FIXED HANDLES)



Type V 6U




Type I, II Ejector Style




FPE04-3U

Type V, 3U Fixed Handle Style



FP04-3U

Standard Filler Panels



Captive sleeves/screws are included with all VectorPak™ filler panels and also sold separately in a hardware kit:

P/N HD99-1

Includes	Qty
Black plastic sleeve	48
M2.5 x 11 mm, nickel plated steel screw	48

Filler Panels/Blank-off Plates Features

- Covers unused slots
- Improves air flow
- Mounting hardware included

Typical slot width is 0.800" (4HP)
Material: 6063T5, extruded brushed Aluminum with clear Iridite finish.


Each Filler Panel Kit Includes

4,8 or 12HP panel (0.8", 1.6" or 2.4")


M2.5 Nickel plated mounting screws with 'captive' sleeves

U	Part Number 4HP	Part Number 8HP	Part Number 12HP
3	5231304-07	5231308-07	5231312-07
6	5261304-07	5261308-07	5261312-07
9	5291304-07	5291308-07	5291312-07

3U FILLER PANELS



6U FILLER PANELS



Non EMC
Subracks

2 x .123
2 x .294


Top Handle
only for 6U & 9U

PANEL HEIGHT	A
3U	5.067
6U	10.317
9U	15.567

.110 x .150
OBROUND

2 x .294
2 x .123

PANEL WIDTH	B
4 HP	0.788
8 HP	1.588
12 HP	2.388



8HP Handle

4HP Handle

12HP ID Plate

Shown 12HP
Bottom Handle
Configuration

M2.5 x 8 Flat
Head Screw

Retainer Sleeve

M2.5 x 10
Filister Head Screw

ID Plate

M2.5 x 16
Filister Head Screw

Washer

Plastic Handle


M2.5 x 11
Captive Screw

'L' Brackets

PC Board

M2.5 x 0.45
Hex Nut

3U-8HP



Optional
for 6U & 9U
High Panel
VECTOR P/N# HD102

