


**STRADA-DW-GD LENSES FOR OSRAM-OS
DRAGON SERIES OF LEDs**

- Specially designed for Osram-os Golden Dragon Plus LEDs.
- New extremely wide SIDE-EMITTING design with very and uniform light distribution.
- Lens material optical grade PMMA. Allows use of high current and temperature conditions
- Best available optical efficiency, approximately 92%.
- Fastening to heat sink with or without PU foam adhesive tape of automotive grade, please select which suits the best for your needs.


LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Strada-DW-GD	C11132_Strada-DW-GD	$\pm 48^\circ - \pm 74^\circ$
Strada-DW-GD-TAPE	CA11180_Strada-DW-GD-tape	$\pm 48^\circ - \pm 74^\circ$

EULUMDAT & IES FILES AVAILABLE BY REQUEST


MEASUREMENT DATA

Relative Intensity of C11132_Strada-DW-GD



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWING



© Ledil Oy – PRELIMINARY - Subject to change without prior notice