

D

C

B





A

D

C

B

A



- 1 HOUSING: NYLON, UL 94V-0 RATED, BLACK.
- 2 CONTACTS & GROUND CONTACT: 2.54µm [.000100] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- 3 ACCEPTS #2 SELF-TAPPING SCREW, .250 LONG REF.
- 4 CIRCUIT IDENTIFICATION IS BASED ON THE INDUSTRY STANDARD. THE VIEW OF THE COMPONENT SIDE OF THE PANEL.
- 5 CONTACTS & GROUND CONTACT: BRASS PER ASTM B36.

5212476-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA 11-12-04 CHK C. ROHDE 11-12-04 APVD M. WALMSLEY 11-12-04		tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-10047		NAME RECEPTACLE ASSY, 5 POSITION, CIRCULAR DIN	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 0° 30'		APPLICATION SPEC 114-40025		SIZE A2	
MATERIAL 1 5		FINISH 2		WEIGHT -		CAGE CODE 00779	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	
				REV 01		RESTRICTED TO -	