

Technical datasheet: FT-10.5T-9.0A1-462

Specifications:

Resonant Frequency	8.5kHz $\pm$ 0.5kHz
Max Resistance (Zr)	700 Ω
Capacitance	9000nF $\pm$ 30%nF

Dimensions:

Type A: (D: Ø10.5mm, d: Ø7.5mm, T: 0.14mm, t: 0.07mm)

