

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090029](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow Nylon 26W Fluorescent Hand Lamp with Switch and Grips Molded, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')



Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E59049
General	
Product Family	Portable Lighting
Series	130109
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Name	Pro-Yellow
Type	Hand Lamps
UPC	78678852922
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Commercial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	N/A
Material - Guard	Polycarbonate
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTW
Lamp Type	PL-C 26/41/4P
Lamp Wattage - Maximum	26W
Lumens	1800
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	WT6F-50

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130109](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION