

Sleeve housing - VC-K-T2-IN (10-25) G - 1583880

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sleeve housing, plastic, type: VC2, black, with integrated cable entry 10 x 25 mm in diameter, V2A locking screws with Allen screw head.

Product Features

- ✓ Plastic housing with straight cable outlet and cable gland.
- ✓ Variable grommet with a seal area for a cable diameter of 10 mm - 25 mm.



Key commercial data

Packing unit	1 PCE
Weight per Piece (excluding packing)	100.0 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	81 mm
--------	-------

Ambient conditions

Degree of protection	IP65, IP67, IP68
Ambient temperature (operation)	-40 °C ... 80 °C

General

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Design	VC2
Degree of protection	IP65, IP67, IP68
Inflammability class according to UL 94	V0
Locking type	Screw locking
Fixing screws	M4 (3 mm Allen screw)

Sleeve housing - VC-K-T2-IN (10-25) G - 1583880

Technical data

General

Tightening torque, mounting screw	1.5 Nm $\pm$ 0.3 Nm
Type of the screw connection	Pg29
Pg screw connection	With
Cable exit	Straight
Housing material	Polyamide
Seal material	NBR
Ambient temperature (operation)	-40 °C ... 80 °C

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27371205
eCl@ss 5.1	27371205
eCl@ss 6.0	27371205
eCl@ss 7.0	27371205
eCl@ss 8.0	27371205

ETIM

ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

GOST

Sleeve housing - VC-K-T2-IN (10-25) G - 1583880

Approvals

Ex Approvals


Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing



Dimensioned drawing

