

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |

NOTES:

Insulator Material: Nylon-6T, UL 94V-0

Contact Plating: TIN, 80-100μ”

Contact Material: Brass





Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



PCB LAYOUT

| NUMBER<br>OF POSITIONS | DIMENSIONS |       |
|------------------------|------------|-------|
|                        | A          | B     |
| 06                     | 4.00       | 13.30 |
| 08                     | 6.00       | 15.30 |
| 10                     | 8.00       | 17.30 |
| 12                     | 10.00      | 19.30 |
| 14                     | 12.00      | 21.30 |
| 16                     | 14.00      | 23.30 |
| 18                     | 16.00      | 25.20 |
| 20                     | 18.00      | 27.30 |
| 24                     | 22.00      | 31.30 |
| 26                     | 24.00      | 33.30 |
| 30                     | 28.00      | 37.30 |
| 34                     | 32.00      | 41.30 |
| 40                     | 38.00      | 47.30 |
| 44                     | 42.00      | 51.30 |
| 50                     | 48.00      | 57.30 |
| 60                     | 58.00      | 67.30 |
| 64                     | 62.00      | 71.30 |



| UNLESS TOLERANCE                                                                   |                                                                                     | DRAW BY    |       | Cnc Tech,LLC |                 |
|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------|-------|--------------|-----------------|
| GENERAL                                                                            | ANGLE                                                                               | DESIGN BY  |       |              |                 |
| X. ± 0.30                                                                          | X.° ± 3.0°                                                                          | CHECK BY   |       |              |                 |
| .X ± 0.20                                                                          | .X° ± 2.0°                                                                          |            |       |              |                 |
| .XX ± 0.15                                                                         | .XX° ± 1.0°                                                                         | APPROVE BY |       |              |                 |
| .XXX ± 0.08                                                                        | .XXX ± 0.5°                                                                         |            |       | Part NO.     |                 |
|                                                                                    |                                                                                     | SCALE      | SHEET | UNIT         | 3120-XX-0300-99 |
|                                                                                    |                                                                                     | 1:1        | 1/1   | MM           |                 |
|  |  |            |       |              |                 |
|                                                                                    |                                                                                     | DRAW NO:   |       | REV: A       |                 |