




- | | | | | | | | | |
|---|-----------------------|-------|---------|--------|---------|----|---|------------|
| 9 | OBSOLETE | -2.54 | [.100] | 5.08 | [.200] | 2 | 6 | 3-146386-9 |
| | | 99.06 | [3.900] | 101.60 | [4.000] | 40 | | 3-146386-8 |
| | | 96.52 | [3.800] | 99.06 | [3.900] | 39 | | 3-146386-7 |
| | | 93.98 | [3.700] | 96.52 | [3.800] | 38 | | 3-146386-6 |
| | | 91.44 | [3.600] | 93.98 | [3.700] | 37 | | 3-146386-5 |
| | | 86.36 | [3.400] | 88.90 | [3.500] | 35 | | 3-146386-4 |
| | | 83.82 | [3.300] | 86.36 | [3.400] | 34 | | 3-146386-3 |
| | | 78.74 | [3.100] | 81.28 | [3.200] | 32 | | 3-146386-2 |
| | | 71.12 | [2.800] | 73.66 | [2.900] | 29 | | 3-146386-1 |
| | | 68.58 | [2.700] | 71.12 | [2.800] | 28 | | 3-146386-0 |
| | | 66.04 | [2.600] | 68.58 | [2.700] | 27 | | 2-146386-9 |
| | SUPERSEDED 7-146386-8 | 60.96 | [2.400] | 63.50 | [2.500] | 25 | | 2-146386-8 |
| | | 58.42 | [2.300] | 60.96 | [2.400] | 24 | | 2-146386-7 |
| | | 55.88 | [2.200] | 58.42 | [2.300] | 23 | | 2-146386-6 |
| | | 50.80 | [2.000] | 53.34 | [2.100] | 21 | | 2-146386-5 |
| | | 45.72 | [1.800] | 48.26 | [1.900] | 19 | | 2-146386-4 |
| | | 43.18 | [1.700] | 45.72 | [1.800] | 18 | | 2-146386-3 |
| | | 40.64 | [1.600] | 43.18 | [1.700] | 17 | | 2-146386-2 |
| | | 38.10 | [1.500] | 40.64 | [1.600] | 16 | | 2-146386-1 |
| | | 35.56 | [1.400] | 38.10 | [1.500] | 15 | | 2-146386-0 |
| | 9 | 7.62 | [.300] | 10.16 | [.400] | 4 | | 1-146386-9 |
| | | 73.66 | [2.900] | 76.20 | [3.000] | 30 | | 1-146386-8 |
| | | 88.90 | [3.500] | 91.44 | [3.600] | 36 | | 1-146386-7 |
| | | 81.28 | [3.200] | 83.82 | [3.300] | 33 | | 1-146386-6 |
| | | 76.20 | [3.000] | 78.74 | [3.100] | 31 | | 1-146386-5 |
| | | 63.50 | [2.500] | 66.04 | [2.600] | 26 | | 1-146386-4 |
| | | 53.34 | [2.100] | 55.88 | [2.200] | 22 | | 1-146386-3 |
| | | 48.26 | [1.900] | 50.80 | [2.000] | 20 | | 1-146386-2 |
| | | 33.02 | [1.300] | 35.56 | [1.400] | 14 | | 1-146386-1 |
| | | 30.48 | [1.200] | 33.02 | [1.300] | 13 | | 1-146386-0 |
| | | 27.94 | [1.100] | 30.48 | [1.200] | 12 | | 146386-9 |
| | | 25.40 | [1.000] | 27.94 | [1.100] | 11 | | 146386-8 |
| | | 22.86 | [.900] | 25.40 | [1.000] | 10 | | 146386-7 |
| | | 20.32 | [.800] | 22.86 | [.900] | 9 | | 146386-6 |
| | | 17.78 | [.700] | 20.32 | [.800] | 8 | | 146386-5 |
| | | 15.24 | [.600] | 17.78 | [.700] | 7 | | 146386-4 |
| | | 12.70 | [.500] | 15.24 | [.600] | 6 | | 146386-3 |
| | | 10.16 | [.400] | 12.70 | [.500] | 5 | | 146386-2 |
| 9 | SUPERSEDED 5-146386-1 | 5.08 | [.200] | 7.62 | [.300] | 3 | | 146386-1 |

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWG	M.BINNER	05NOV02			TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK		J.O'LESON	05NOV02	NAME	REC.ASSY.MD IV, SR., 100CL VRT BOARD MOUNT,CLOSED,TE SHORT PNT. OF CONTACT		
				EXP'D		J.O'LESON	05NOV02				
		0 PLC		± -	PRODUCT SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		2 PLC		± -	108-25022						
		3 PLC		± 0.25[.010]	APPLICATION SPEC						
		5 PLC		± 0.13[.005]	114-25018						
MATERIAL 		ANGLES		± -	WEIGHT		A1	00779		146386	—
		FINISH		SEE TABLE							
CUSTOMER DRAWING											
				SCALE		4:1		SHEET		1 of 1	
				REV		K0					