

Schneider Electric USA

1415 South Roselle Road

Palatine, IL 60067

Customer Care Center: 1-888-778-2733

Web: www.schneider-electric.us**Item # ATV12HU15M3, Variable Speed Drive****Variable Speed Drive**

Variable Speed Drive

SPECIFICATIONS

Family	Altivar 12
Product Line	AC Drives
Output Ampere Rating	7.5
Application	Variable & Constant
Enclosure Rating	IP20
Frame Size	B
HP Rating	2
kW Rating	1.5
Voltage Rating	230/230VAC
Input Phase	3 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	4
Analog Input	1

Analog Output	1
Logic/Relay Outputs	1 protected relay output, 1 N/O contact and 1 N/C
Weight [lb]	2.64
Weight [kg]	1.20
UL File No.	E116875
CSA File	2159172
Other	CE, GOST, RoHS, NOM, EMITECH,UL
Communication	Modbus

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV12HU15M3](#)