

SKINDICHT® SHV-VITON

Water-proof gland to meet maximum quality requirements

**SKINDICHT®
SHV-VITON**
with sealing cone of Viton,
compression water-proof,
10 bar


The SKINDICHT® SHV-VITON
sealing cable gland is a special
compression water-proof gland
to meet maximum quality
requirements.

The conical special sealing
element of Viton guarantees
extensive sealing, which in
turns helps achieve excel-
lent resistance under pres-
sure and strain-relief.

Suitable accessories see
page 447.

The Viton sealing cone
demonstrates outstanding
resistance to oils and bio-
logical oils, solvents and
chemicals at high tempera-
tures up to 200 °C.

Suitable accessories see
page 447.



Viton® = registered trademark of Du Pont de Nemour

Technical Data



Material:
Body: Nickel-plated brass
Sealing cone: Viton
O-ring: Viton



Protection class: IP 68 – 10 bar



Temperature range:
-15 °C to +200 °C

Part Number	Type PG-size		Clamping range diameter mm	Wrench size 1/2 mm	C mm	D mm	Pack size pieces
SKINDICHT® SHV-VITON							
5202 4934	SHV-V	7/7/5	3,8 - 4,8	14	26	5	50
5400 0015	SHV-V	9/9/6	4,8 - 5,8	17	28,5	6	50
5202 4935	SHV-V	9/9/7	5,8 - 6,8	17	28,5	6	50
5202 4936	SHV-V	11/11/7	5,8 - 6,8	20	31	6	25
5202 4937	SHV-V	11/9/1/9	6,8 - 8,8	20	31	6	2,5
5202 4970	SHV-V	13,5/9/11	8,5 - 10,8	22	33	6,5	25
5202 4968	SHV-V	13/11/9	6,8 - 8,8	22	33	6,5	25
5202 4969	SHV-V	13,5/11/11	8,5 - 10,8	22	33	6,5	25
5202 4961	SHV-V	13,5/13,5/9	6,8 - 8,8	22	33	6,5	25
5202 4962	SHV-V	13,5/13,5/11	8,5 - 10,8	22	33	6,5	25
5202 4971	SHV-V	16/11/13	10,8 - 12,8	24	35	6,5	25
5202 4973	SHV-V	16/13,5/13	10,8 - 12,8	24	35	6,5	25
5202 4964	SHV-V	16/16/13	10,8 - 12,8	24	35	6,5	25
5202 4965	SHV-V	16/16/15	13,8 - 14,8	24	35	6,5	25
5202 4966	SHV-V	21/21/18	15,8 - 17,8	30	38	7	25
5202 4967	SHV-V	21/21/20	17,5 - 19,8	30	38	7	25
5202 4974	SHV-V	29/29/22	19,5 - 21,8	40	44,5	8	10