

CATALOG LISTING

604HE3-6

PAGE 1 OF 1

REPLACES

PR-21132

CHECK

REVISIONS

A PR-21132

TSM

31 MAY 93

B C093183

J A S

12 JUN 98

CHECK




DDM/CAD


DRAWN

TSM

31MAY94

CHECK



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION 		
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE — — — — 5 –12 LB		CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE --- 30 LB MAX		4X S P D T			
RELEASE FORCE — — — — — 3 LB MIN		LOAD	28 VDC		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL — — — — — .040 MAX			SEA LEVEL & 100,000 FT.		
DIFFERENTIAL TRAVEL — — — .020 MAX		RES	4		
OVERTRAVEL — — — — — .125 MIN		IND	4		
		MOTOR	4		
				WEIGHT	

- NOTES
- 1 – CORROSION RESISTANT STEEL ENCLOSURE
 - 2 – SWITCH SEALED PER MIL-S-8805 SYMBOL 5
 - 3 – COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 INCH OF PLUNGER TRAVEL
 - 4 – CIRCUIT DIAGRAM, AND CATALOG LISTING SHOWN ON NAMEPLATE
 - 5 – REPLACEMENT MOUNTING HARDWARE – PACKET 19PA9
 - 6 – FOR OPERATION IN TEMPERATURE OF MINUS 65°F TO PLUS 257°F
 - 7 – HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[604HE3-6](#)