

Model P160
 16mm Rotary Potentiometer
 Conductive Plastic Element
 100,000 Cycle Life
 Metal shaft / Bushing
 Multi – Ganged available
 RoHS Compliant



MODEL STYLES

Side Adjust , Solder Lugs	P160KNP
Side Adjust , PC pins	P160KN
Side Adjust , PC Pins, Long pins	P160KN2
Rear Adjust, PC pins	P160KNPD

ELECTRICAL¹

Resistance Range, Ohms	500-1M
Standard Resistance Tolerance	± 20%
Residual Resistance	20 ohms max.
Power rating Input Voltage, maximum	200 Vac max.
Power Rated, Watts	0.2W- B taper, 0.1W-others
Dielectric Strength	500Vac, 1 minute
Insulation Resistance, Minimum	100M ohms at 250Vdc
Sliding Noise	100mV max.
Actual Electrical Travel, Nominal	260°

MECHANICAL

Total Mechanical Travel	300°± 10°
Static Stop Strength	90 oz-in
Rotational Torque	0.5 to 1.25 oz-in


ENVIRONMENTAL

Operating Temperature Range	-20°C to +70°C
Rotational Life	100,000 cycles

¹ Specifications subject to change without notice.

Model P160

ORDERING INFORMATION²



Shaft Types

E-TYPE

L	10	15	20	25	30	35	40
T	7	10	12	12	12	12	12

F-TYPE


L	15	18	20	25	30	35
T	7	10	12	12	12	12

Q-TYPE

L	10	12	13	14	15	17	20	25	30	35	45
T	2.5	4.5	4	5	6	8	10	12	12	12	12

Shaft Position (F-Type Shaft)

Dashed lines on Type "C" and Type "A" shows position of adjustment slot for E-Type and Q-Type shafts



STANDARD RESISTANCE VALUES, OHMS

500 1K 2K 5K 10K 20K 50K 100K 200K 500K 1MEG


CIRCUIT DIAGRAM




Model P160

OUTLINE DRAWING

Model P160KNP (Side Adjust , Solder Lugs)




Model P160KN (Side Adjust , PC pins)




² Contact our customer service for custom designs and features.

Model P160

Model P160KN2 (Side Adjust , PC Pins, Long pins)



Model P160KNPD (Rear Adjust , PC Pins)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BI Technologies:

[P160KN-0Q15A100K](#)

TT electronics:

[P160KN2-0ECB1MEG](#) [P160KNP-0QD20B50K](#) [P160KNP-0EC25B5K](#) [P160KN-0FC18C2K5](#) [P160KNP-0QC15B200K](#) [P160KN-1EC20B20K](#) [P160KN2-0QA25B1K](#) [P160KNP-0QC20B100K](#) [P160KNPD-4QC15A5K](#) [P160KNP-0Q20B10K](#) [P160KNP-0QC20B50K](#) [P160KN2-0ECB50K](#) [P160KN2-0EC15B50K](#) [P160KN2-0ECB100K](#) [P160KN2-0EB10B100K](#) [P160KN-0EC15B100K](#) [P160KNP-0QC15B200K](#) [P160KN-0QC15B250K](#) [P160KN2-0QA25B10K](#) [P160KNPD-4QA15A5K](#) [P160KNP-0QC15B50K](#) [P160KN2-0EC15B10K](#) [P160KN2 0QC17B50K](#) [P160KNP-0QC15B10K](#) [P160KN-0E15B25K](#) [P160KN-0EC15A500K](#) [P160KN-0EC15A5K](#) [P160KN-0EC15B1MEG](#) [P160KN-0Q15B1MEG](#) [P160KN2-0QC17B10](#) [P160KN2-0QC17B100K](#) [P160KNP-0EA15A20K](#) [P160KNP-0EC15A100K](#) [P160KNP-0EC15A10K](#) [P160KNP-0EC15A1MEG](#) [P160KNP-0EC15B250K](#) [P160KNP-0EC15B25K](#) [P160KNP-0EC15B2K](#) [P160KNP-0QC20A500K](#) [P160KNP-1FD15B10K](#) [P160KNP-4FB20B10K](#) [P160KNP-4FC15B100K](#) [P160KNPD-0EC25C20K](#) [P160KN-0QC15A100K](#) [P160KNP-0EC15B10K](#) [P160KNP-0EC15A250K](#) [P160KN-0EA15B10K](#) [P160KNP-0EC15B100K](#) [P160KN-1QC15B10K](#) [P160KNP-0QC20A100K](#) [P160KNP-0QC20B4K7](#) [P160KNP-0QC20A250K](#) [P160KNPD-0FB25B100K](#) [P160KNP-0FC25B10K](#) [P160KN-0EC20B1MEG](#) [P160KNP-0QC10B10K](#) [P160KNP-1EC20B10K](#) [P160KNP-0QC15B100K](#) [P160KN-0QC15A250K](#) [P160KNP-0EC15B500K](#) [P160KNP-0FC20B10K](#) [P160KNP-0QC20C500K](#) [P160KN-0QC15C250K](#) [P160KNP-0E15C500K](#) [P160KNPD-0EC25C500K](#) [P160KNP-0EA20A50K](#) [P160KNP-0EC15C500K](#) [P160KNP-0QC2B100K](#) [P160KNP-0E15B5K](#) [P160KN2-0QC20B100K](#) [P160KN2-0QC15B1MEG](#) [P160KN-0QC15B1K](#) [P160KNP-0EA15A1MEG](#) [P160KNP-0FB15B10K](#) [P160KNP-0QD2B100K](#) [P160KN-0QC20B10K](#) [P160KNP-0FC25A10K](#) [P160KNP-0QC20A25K](#) [P160KNP-0FC10B100K](#) [P160KNP-0FD20A100K](#) [P160KNP-0FC25B50K](#) [P160KNPD-0QA17B1K](#) [P160KNP-0FC15B10K](#) [P160KNP-0QC20A10K](#) [P160KNP-0QC20B25K](#) [P160KNP-0QC15A1K](#) [P160KNP-0E15C200K](#) [P160KN-0EA15A100K](#) [P160KNP-0QC20B250K](#) [P160KNP-0QC20B500K](#) [P160KNP-0QC15C100K](#) [P160KNPD-0QC15A10K](#) [P160KNP-0FC18B100K](#) [P160KNP-2FD15B10K](#) [P160KNP-0QC20A1MEG](#) [P160KNP-0EC15C1MEG](#) [P160KNP-0FC15A10K](#) [P160KN-0FD18C10K](#) [P160KN-0QC15C500K](#) [P160KN-0FC20A1MEG](#)