

TOOLS

CRIMPING TOOL for "D" SUBMINIATURE CONNECTORS



Hand held tool crimps D-Sub pins (male and female) with a single squeeze on the contact material. Has built-in wire cutter. PVC handle allows crimping in comfort.

No. WS26

PROFESSIONAL D-SUB CONTACT RATCHET CRIMPING TOOL



No. YAC4
D-Sub Contact Crimping Tool

- Precision
- High Quality
- Durable
- 18-22 AWG, 24-30 AWG
- Six section pressure adjustment
- For female and male D-subminiature contacts

CRIMPING TOOL for "F" CONNECTORS

For a tight, permanent crimp, this ferrule tool does the proper job every time. Two slots are provided for RG59/U and RG58/U coaxial cable.



No. WS17

ECONOMY HEX CRIMPING TOOL

For a tight and permanent crimp. Designed for coaxial fittings on RG59/U, RG62/U and RG6/U. PE insulation grip handle for comfort and maximum crimping force. Made of tempered steel. 8" long.



No. 12-170

PROFESSIONAL HEX CRIMP TOOL


Perfect for CATV, MATV and TVRO installations, when heavy duty crimping is required. It's light enough to fit conveniently in an installers belt. Features cushion plastic handles for comfortable gripping. 9" overall length.



Works for all Philmore crimp-on connectors for **No. WS25** - Crimps RG59/U, RG6/U stated wire type: 'F', BNC, TNC, UHF, Mini **No. WS27** - Crimps RG58/U, RG59/U and Pin Crimping Position **No. WS29** - Crimps Philmore Pro-Crimp "F" connectors, RG11/U

PROFESSIONAL RATCHET COAXIAL CRIMPING TOOL

For CATV, MATV, and TVRO installations. This economically priced tool is just right for the professional installer and hobbyist alike. Small enough to fit in the tool belt and rugged enough for any job. It works with most "F", BNC, TNC, UHF, Mini-UHF, SMA, & RCA connectors



Features

Heavy-duty Steel construction
Insulated Handle
Non-replaceable Drop-forged jaws
Overall length 9" (229mm)
Hex Crimp for RG 59, RG62 (.255") RG6, (.322")

No. 63-116 Professional Ratcheting Hex Crimp Tool
RG59, RG62, and RG6

Professional Ratchet Crimp Tool w/ Interchangeable Dies

- Full cycle ratchet mechanism with quick release safety lock
- High carbon steel ratchet frame
- PE insulation grip handle for comfort and maximum crimping force
- Interchangeable dies for F, BNC, TNC, N, Teflon, Thinnest-PVC / Teflon and Fiber-Optic connectors



No. WS28 - (RG58/U, RG59/U and 1/16" pin)

No. WS34 - For Insulated Terminals: (22-18 AWG, 16-14 AWG and 12-10 AWG)

No. WS36 - (RG58/U, RG59/U and RG6/U)

INTERCHANGEABLE CRIMP DIES

for Nos. WS28, WS34, WS36

Part No. Dies Only	Hex	Oct	Sq	Pin	Sq	Pin	For Crimping RG Type Cable
No. WS74	.256"	.213"		.068"			59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic
No. WS76	.319"	.213"	.187"				6, 55, 58, 141, 142, 223, 303, 400, 174, Fiber Optic
No. WS78	.319"	.256"	.213"		.068"		6, 59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic.
No. WS80	.255"	.213"	.137"	.100"	.069"	.043"	59, 62, 8X, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic
No. WS82	.178"	.151"	.128"	.078"	.068"	.042"	122, 174, 179, 180, 187, 188, 195, Fiber Optic 178, 316, BELDEN 8218.
No. WS84		.255"	.213"	.187"	.068"		55, 58, 59, 62, 140, 141, 142, 210, 223, 174, 303, 400, Fiber Optic, BELDEN 8279.
No. WS88	Coded: Red 22-18 Blue 16-14 Yellow 12-10						Insulated Terminals 10-22 ga.