

**Industrial Ethernet
IE-PS-V04P-2LC-MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with LC insert

General ordering data

Type	IE-PS-V04P-2LC-MM
Order No.	1963320000
Version	FO connector, Variant 4, LC-Duplex multi-mode, IP 67
GTIN (EAN)	4032248651795
Qty.	10 pc(s).

Industrial Ethernet
IE-PS-V04P-2LC-MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 35.3 g

Temperatures

Operating temperature -40 °C...70 °C Storage temperature
 Installation temperature

Downloads

GOST Approval POC
 DE.ME25.B01411.pdf

General data

Colour	Miscellaneous	Connection 1	LC
Connection 2	LC	Description of article	Variant 4, LC-Duplex multi-mode
Fibre type	Multimode	Housing main material	PA UL 94 V0
Insertion loss	0.5 dB singlemode, 0.4 dB multimode	Plugging cycles	500
Protection degree	IP 67	Return loss (attenuation)	40 dB singlemode; 30 dB multimode
Sheath diameter, max.	10 mm	Sheath diameter, min.	5 mm

Standards

Connector standard IEC 61076-3-106 Var. 4,
 IEC 61754-20

Classifications

ETIM 3.0	EC001121	ETIM 4.0	EC002641
ETIM 5.0	EC002641	ETIM 6.0	EC002641
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-08
eClass 6.2	27-26-07-08	eClass 7.1	27-25-05-04

Approvals

Approvals



ROHS Conform

Industrial Ethernet IE-PS-V04P-2LC-MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing

