



A

クレモン

ローラー
締り

特装密閉
ハンドル

フリーザー
密閉

平面
スイング
HANDLES

ギア式

平面
ハンドル

ポップ
ハンドル

リフト
ハンドル

アジャスト
ハンドル

ラッチ式

スナッチ

リンク

フック式

ロック
ハンドル

L 型
ハンドル

T 型
ハンドル

丸型
小型

押ボタン

取手

つまみ

止め金
ロッド棒

ジョイント
リンク

ワイヤ

18.05

アウトサイドガasketハンドル OUTSIDE GASKET HANDLES



A-462
亜鉛合金製

特徴 Feature

- バックの外側にハンドルを取付けるので、防水を必要とする際にハンドル取付け部にコーキング等を施す必要がありません。
- シーリングエリア外にハンドルを取付ける為、庫内のスペースを有効に利用できます。
- スリムなボディで大きなストローク(32mm)が得られます。
- 筐体の大きさが変わっても、ロッドの長さを変える必要がありません。
- ロッド受けと推奨ヒンジB-71-3とは、取付けに互換性があります。またハンドルのパネル穴明けも上下対称となっている為、筐体の設計が容易に行えます。(扉の勝手を選びません)
- 錠前は操作性に優れた防塵シャッター付新型リバーシブルキー-TAK60を標準装備(A-462-1-1-TAK60)
- 右用・左用・鍵付・鍵なしがあります。
- The handles are attached outside of the packing so no calking etc is needed for the handle fixed parts when making theses watertight.
- The handles are attached outside of the sealing area so the inside spaces can be used maximum.
- Their body is slim and also a large stroke of 32mm can be obtained.
- It is not necessary to change the rod length no matter how the case needs to be changed in size.
- The rod catch and the recommended hinge B-71-3 are interchangeable when fixing. Also the upper and lower handle panel drilling holes are symmetrical so it is easy to design the case (these can be used with various doors).
- The lock comes standard with the TAK60, a new-style reversible key with an easy-to-use dustproof shutter. (A-462-1-1-TAK60)
- Right-hand use or Left-hand use, with lock or without lock.

仕様 材質

- 本体・ローラー受け/亜鉛合金(ZDC)
- ローラーユニット/冷間圧延鋼板・ポリアセタル(POM)
- スリーブ・受け/冷間圧延鋼板(SPCC)
- 表面仕上
- 本体/サチライトクロムめっき(MZCr)
- スリーブ・受け/亜鉛めっきクロムめっき処理(MFZn-C)
- ローラー受け/亜鉛めっきクロムめっき処理(MFZn-C)


- 鍵番号: TAK60・0200
- 付属品: キー2本・スリーブ2個・ローラー受け2個・受け・ローラーユニット2個・CS型止め輪2個・スペーサー・ハンドル回転指示シール1枚
- 適用板厚: 1.6~2.3mm(1.6mmの扉に取付ける場合のみ付属のスペーサーをご使用ください。)
- 通信用ラック
- 標準品・・・納期お問合せください
- マスターシステム、指定同番、鍵違い、鍵なしも製作します。お問合せください。
- その他のロッド長さを希望の場合は、お問合せください。
- 観音扉仕様も製作致します。お問合せください。
- 本製品の止め金取付け用ねじは、緩み防止のため「緩み防止剤」の塗布をお奨め致します。

Specifications



- Material
- Main body・roller catch: Zinc alloy (ZDC)
- Roller unit : Cold rolled steel (SPCC), polyacetals (POM)
- Sleeve catch: Cold rolled steel (SPCC)
- Finish
- Main body: Satellite chrome plating (MZCr).
- Sleeve/Catch: Zinc plating chrome treatment (MFZn-C).
- Roller catch: Zinc plating chrome treatment (MFZn-C).

- Key No.: TAK60 ,0200
- Accessories: Two keys, two sleeves, two roller catches, catch, two roller units, two CS stopper rings, spacer and one sticker indicating which way to turn the handle.
- Applicable panel thickness: 1.6 to 2.3mm (Use the spacer in case of 1.6mm)
- Communication racks.
- For rods with various lengths, consult us.
- It is recommended that thread-locking fluid be used to prevent loosening of the mounting screws for the catch.



Specific use Remarks



A-462-1-1R (右開き用)
Right-hand use



商品番号 Product No.	備考 Remarks	鍵番号 Key No.	製品質量(g) Mass	コード Code	単価 Price	数量 Quantity	量販価格 Bulk Price
A-462-1-1L-TAK60	● 2D	TAK60	640	04091	¥6,400	5個~	¥6,144
A-462-1-1L	● 2D	0200	640	03294	¥6,400	5個~	¥6,144
A-462-1-2-L	● 2D	鍵なし Without lock		03320	¥5,500	5個~	¥5,280
A-462-1-1R-TAK60	● 2D/3D	TAK60	640	04092	¥6,400	5個~	¥6,144
A-462-1-1R	● 2D	0200	640	03205	¥6,400	5個~	¥6,144
A-462-1-2-R	● 2D	鍵なし Without lock		03319	¥5,500	5個~	¥5,280



商品番号 Product No.	備考 Remarks	鍵番号 Key No.	製品質量(g) Mass	コード Code	単価 Price	数量 Quantity	量販価格 Bulk Price
A-462-1-1L-TAK60	● 2D	TAK60	640	04091	¥6,400	5個~	¥6,144
A-462-1-1L	● 2D	0200	640	03294	¥6,400	5個~	¥6,144
A-462-1-2-L	● 2D	鍵なし Without lock		03320	¥5,500	5個~	¥5,280
A-462-1-1R-TAK60	● 2D/3D	TAK60	640	04092	¥6,400	5個~	¥6,144
A-462-1-1R	● 2D	0200	640	03205	¥6,400	5個~	¥6,144
A-462-1-2-R	● 2D	鍵なし Without lock		03319	¥5,500	5個~	¥5,280