



UNIT:mm




CONN OUTER MOLD: WM-020

P1



CONN OUTER MOLD: WM-021



P2


2500±50mm

PIN ASSIGNMENT

P1 RED P2
1 WHITE 1
2 SPIRAL 2
3 3

Electronic Test:

- 1.100% Test,(Open,Short,Miss Wire)
- 2.Contact Resistance:2 ohm max.
- 3.Insulation Resistance:1M ohm min.
- 4.Hi-Pot:300V DC/10ms



⑧	TIE	1	BLACK L=80mm
⑦	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*1.15mm.
⑥	PE BAG	1/10	CLEAR SIZE:280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑤	PE BAG	1	CLEAR SIZE:130*230*0.05mm PRINT BLACK"MADE IN CHINA"
④	OUT JACKET	5.5g	OUTER MODEL PVC 45P COLOR BLACK
③	CONN	1	3.5ST FEMALE OD8.0*ID3.5mm L=23mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
②	CONN	1	3.5ST MALE Tray6.0mm L=30mm MOLD TYPE NI-PLATED INSULATOR COLOR:BLACK
①	CABLE	1	NOUL 28AWG(7/0.12 TC)*2C(RED,WHITE)*S(43/0.12 TC) JACKET BLACK OD:3.0MM L=2500±15mm.
NO.	NAME	Q'TY	SPECIFICATION

Cnc Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	ZHONGHS	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	770-10041-00250
DECIDE BY		DATE	2012-02-06
VERSIONS/EDITEDN	A/0	PROJECTION	