



Series: EDJ

Shunts


- ❖ Dual wipe contacts
- ❖ Side and end stackable
- ❖ Mates to 2.54 mm pin headers
- ❖ Mates to 2.00 mm pin headers




EDJ1 (CLOSED INSULATOR)




EDJ2 (OPEN INSULATOR)




EDJ3 (SHORT INSULATOR)



EDJ5 (2.0 mm)



EDJ4 (WITH HANDLE)



Specifications

Shunts

EDJ

Ratings:	
Current	3A
Dielectric strength	AC 650 V RMS for 1 minute
Contact resistance	20 mΩ max.
Insulator resistance	100 MΩ min.

Material:	
Plastic	PBT, Glass-filled, UL 94V-0
Contact	Phosphor Bronze
Temperature range	-55°C / +105°C

ORDERING PROCEDURE

<u>1</u>	<u>2</u>	<u>3</u>
----------	----------	----------

- 1) Series
- 2) Plating:

Z = Tin
G = Gold
- 3) Color:

0 = Black
1 = Red
2 = White
3 = Blue