

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0047](#)
Status: **Active**
Description: Super-Safeway™ Rubber Hand Lamp with 100W Quick Release Guard with Switch and Receptacle 7.62m (25.0') 16/3 SOOW

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	Side
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678879483
Woodhead	Yes

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	No
Guard Type	Metal Wire
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	181.430/kg
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Material Info

Old Part Number 101USA163



image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130102Series](#)