

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130108-0101](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway™ Twin Tube 80W Fluorescent Work Light, Cord Type 12/3 SOOW Feed Thru 1.22m (4.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR85374  
 UL                        E174254

**General**

Product Family                      Portable Lighting  
 Series                                  [130108](#)  
 NEMA Configuration                NEMA 5-15  
 Outlet                                  Feed-Through  
 Overview                              [Wide-Area Lighting Products](#)  
 Product Literature Order No        987650-8054  
 Product Name                        Super-Safeway™  
 Type                                    Wide Area Lamps  
 UPC                                    78678813032  
 Woodhead                              Yes

**Physical**

Cord Length - Primary                1.22m (4.0')  
 Cord Length - Secondary            0.152m (6.00" )  
 Depth                                  190.75mm (7.510")  
 Duty                                    Industrial  
 Guard Included                        No  
 Guard Type                            N/A  
 Height                                  82.55mm (3.250")  
 Length                                 636.00mm (25.039")  
 Material - Globe                        Butyrate  
 Material - Guard                        Nitrile Rubber 80 Shore A  
 Mounting Style                        Adjustable Brackets  
 Packaging Type                         Carton  
 Socket Construction                    N/A

**Electrical**

Bulb Type                                Fluorescent  
 Cord Type - Primary                 16/3 SJOW  
 Lamp Type                              PL-L 40/41  
 Lamp Wattage - Maximum            80W  
 Lumens                                 5300  
 On/Off Switch                         No  
 Voltage (Fixture) - Maximum        120VAC 60 HZ

**Material Info**

Old Part Number                        1052-PL



**EU RoHS**

**China RoHS**

**Compliance Status**

**Not Reviewed**

**REACH SVHC**

**Not Reviewed**

**Low-Halogen Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130108Series](#)