ED3001/X-FD



1-n poles, Spacing 5.0 mm adjustable to 5.08 mm
insert required no. of poles **x**
How to order see page 5

Ratings:		
Rated Voltage	**300 V**	**250 V**
Rated Current	**16 A**	**24 A (T60)**
Wire Size	**AWG 28-14**	**2.5 mm²**
Test Voltage		**2.0 kV**
Max. Rated Cross Section		
Single Wire (solid)		**2.5 mm²**
Stranded Wire (flexible)		**2.5 mm²**
Stranded wire with Ferrules		**1.5 mm²**
Dimensions		
Spacing		**5.0 mm (5.08 mm)**
PCB Hole Diameter		**1.0 mm (2x)**
Stripped Length		**6.0 mm**
Materials		
Insulating Material		**PA**
Flammability Class		**UL94 V-0**
Temperature Range		**-30°C/+105°C**
Cage Clamp		**Stainless Steel**
Wire Guard		**Cu**
Color		
Slade Grey