



1820

Medium Light

Pocket Sabre™



The Pocket Sabre™ 1820 flashlight descended from Pelican's famous SabreLite™ 2000. Built to last, the unbreakable ABS body resists chemicals, water and corrosion. The polycarbonate lens and focused Xenon lamp module produce a tight white beam that penetrates any hazardous condition. All these features and safety approvals, too. It comes with a twist-on shroud, is submersible, and powered by 2 C alkaline cells.

- Built Pelican tough
- Unconditional Lifetime Guarantee of Excellence
- Submersible
- Super bright Xenon beam

DIMENSIONS

Length: 5.83" (14.8 cm)

MATERIALS

Body: ABS

O-Ring: Ethylene Propylene

Lens: Polycarbonate (PC)

Shroud: K-Resin

Clip: ABS

Contact Spring Retainer: Stainless Steel

COLOURS


 High Visibility Yellow

 Black

LIGHT SPECS

Lamp Type: Incandescent (Xenon)

FL1 STANDARD	HIGH
	22 LUMENS

	6h 45mins
	146m
	5466cd
	IPX7

POWER

Battery Size: C
Battery Type: Alkaline
Battery Quantity: 2
Batteries Included: yes
Volts: 3.0v

WEIGHT

Weight With Batteries: 8.3 oz (235 gr)
Weight Without Batteries: 3.3 oz (94 gr)
Packaged Weight: 9.4 oz (266 gr)

SWITCH

Switch Type: Twisting Lens Shroud
Light Modes: On / Off

CERTIFICATIONS

Class I, Division 2
 Class II, Division 2
 Class III, Division 2
 IECEx ib

OTHER

Submersible: yes
Minimum Pack: 6
Military: yes
Package Code: C

Pelican Products, Inc.

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com