



CK20M

Pipe clamp probe



Copyright © 2007 Test Products International, Inc.

Application

Clamp probe for pipe temperatures

Range°F°C

-58° to 482°F
-50° to 250°C

Probe tip

N/A

Dimensions

Max jaw opening: 0.79
Nominal jaw opening: 0.25"
Lead Length: 39.4" (1M)

Insulation Material

Polyurethane