




Wiha Open End Wrenches

Meets DIN 3110 / ISO10102 Specifications

31CRV3 tool steel forgings
Precision formed for an
exact fitNarrow profile
for better access
in tight locationsWide I-beam for
better grippingSatin Chromed
Sure Grip BodyThe wrench specified by BMW,
Mercedes & Rolls Royce**350 Open End Wrenches Metric DIN 3110 / ISO 10102**

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	AF	AF	OAL	OAL	H	D ¹	D ²		
	mm	mm	mm	Inch	mm	mm	mm	lbs.	pkg.
350 01	4.0 x	5.0	103	4.0	3.3	11.6	13.7	.02	10
350 02	5.0 x	5.5	104	4.1	3.3	13.7	14.7	.02	10
350 03	5.5 x	7.0	122	4.8	3.6	15.7	17.7	.04	10
350 04	6.0 x	7.0	122	4.8	3.6	15.7	17.7	.04	10
350 05	7.0 x	8.0	130	5.1	3.9	17.7	20.8	.06	10
350 06	8.0 x	9.0	140	5.5	3.9	20.8	22.9	.07	10
350 07	8.0 x	10.0	140	5.5	3.9	20.8	22.9	.07	10
350 08	10.0 x	11.0	156	6.1	4.8	23.9	26.9	.12	10
350 09	10.0 x	13.0	172	6.7	5.3	24.0	30.0	.15	10
350 10	12.0 x	13.0	172	6.7	5.3	28.0	31.0	.13	10
350 11	12.0 x	14.0	172	6.7	5.3	28.0	31.0	.13	10
350 12	13.0 x	14.0	190	7.5	5.7	32.5	34.9	.20	10
350 13	14.0 x	15.0	190	7.5	5.7	32.5	34.9	.20	10
350 14	16.0 x	17.0	204	8.0	5.9	36.1	39.2	.23	10
350 15	16.0 x	18.0	204	8.0	5.9	36.1	39.2	.23	10
350 16	18.0 x	19.0	223	8.7	6.5	40.2	42.3	.33	1
350 17	19.0 x	22.0	236	9.3	6.8	44.9	48.4	.42	1
350 18	20.0 x	22.0	236	9.3	6.8	44.9	48.4	.41	1
350 19	21.0 x	23.0	250	9.8	7.3	47.4	51.5	.58	1
350 20	22.0 x	24.0	250	9.8	7.3	47.4	51.5	.57	1
350 21	24.0 x	26.0	265	10.4	7.8	52.5	58.6	.70	1
350 22	24.0 x	27.0	265	10.4	7.8	52.5	58.6	.68	1
350 23	25.0 x	28.0	280	11.0	8.1	55.2	61.3	.77	1
350 24	27.0 x	29.0	280	11.0	8.1	58.6	64.4	.79	1
350 25	27.0 x	30.0	280	11.0	8.1	58.6	64.4	.78	1
350 26	30.0 x	32.0	302	11.8	8.6	64.8	70.3	1.06	1
350 27	32.0 x	36.0	325	12.7	8.8	66.5	74.5	1.21	1
350 28	36.0 x	41.0	358	14.0	8.8	74.5	84.0	1.61	1
350 29	46.0 x	50.0	450	17.6	10.8	93.5	105.0	3.23	1

350 Open End Wrenches Inch DIN 3110 / ISO 10102

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	AF	AF	OAL	OAL	H	D ¹	D ²		
	Inch	Inch	mm	Inch	mm	mm	mm	lbs.	pkg.
350 32	1/4 x	5/16	190	7.5	5.7	32.5	34.9	.20	10
350 33	5/16 x	3/8	204	8.0	5.9	36.1	39.2	.23	10
350 34	3/8 x	7/16	236	9.3	6.8	44.9	48.4	.45	10
350 35	7/16 x	1/2	250	9.8	7.3	47.4	51.5	.58	10
350 36	1/2 x	9/16	190	7.5	5.7	32.5	34.9	.20	10
350 37	9/16 x	5/8	190	7.5	5.7	32.5	34.9	.20	10
350 38	19/32 x	11/16	204	8.0	5.9	36.1	29.2	.24	10
350 39	5/8 x	11/16	204	8.0	5.9	36.1	29.2	.23	10
350 40	5/8 x	3/4	223	8.7	6.5	40.2	42.3	.34	1
350 41	11/16 x	3/4	223	8.7	6.5	40.2	42.3	.33	1
350 42	3/4 x	25/32	236	9.3	6.8	44.9	48.4	.42	1
350 43	3/4 x	7/8	236	9.3	6.8	44.9	48.4	.41	1
350 44	13/16 x	7/8	236	9.3	6.8	44.9	48.4	.40	1
350 45	7/8 x	15/16	250	9.8	7.3	47.4	51.5	.57	1
350 46	15/16 x	1	265	10.4	7.8	52.5	58.6	.68	1
350 47	1 x	1-1/8	280	11.0	8.1	55.2	61.3	.76	1
350 48	1-1/16 x	1-1/4	302	11.8	8.6	59.7	69.9	1.01	1
350 49	1-1/8 x	1-5/16	302	11.8	8.6	64.8	70.3	1.06	1
350 50	1-3/16 x	1-5/16	302	11.8	8.6	64.8	70.3	1.03	1
350 51	1-1/4 x	1-3/8	325	12.7	8.8	66.5	74.5	1.22	1
350 52	1-5/16 x	1-1/2	325	12.7	8.8	66.5	74.5	1.19	1
350 53	1-7/16 x	1-5/8	358	14.0	8.8	74.5	84.0	1.60	1
350 54	1-1/2 x	1-5/8	358	14.0	8.8	74.5	84.0	1.56	1
350 55	1-11/16 x	1-7/8	400	15.7	9.8	84.0	93.5	2.18	1
350 56	1-13/16 x	2	450	17.6	10.8	93.5	105.0	3.22	1