


T-3^{1/4} min screw lamp

W1309



Drawing Not To Scale - All Dimensions in mm.

Type	Size	Rating	Category	Description	Part No.
Incandescent	T10x28	12V 2.2W		T-3 ^{1/4} min screw (MES) lamp	W1309

PHOTOMETRY DATA

Test Volts	Current (mA)			Light output (Lm)			Life (Hours)
	Min.	Nom.	Max.	Min.	Nom.	Max.	
12,0	165	183	201	8,5	11,0	13,5	10,000
13.5	177	196	216	12.8	16,0	19.2	3,000

NOTES

- Lamp base E10/13 in accordance with IEC61-1, (BS EN 60061-1), sheet 7004-22-x.
- C-2V filament shape.
- Lamp shall withstand a cap torsion of 0,3Nm, (2,56lbf. inches).
- Marking: "12V 2,2W" with "SLI" or "VCH" trademark, to be engraved or durably ink-stamped on cap.

SLI Miniature Lighting. Sales Division - B.P. 909 - F-25021 BESANÇON Cedex
Tel: 33 (0)381 477 7 00 - Fax: 33 (0)381 504 233 - e-mail: information@sl-i-socop.com

Technical data subject to modifications without notice. Information included in data sheet is not binding.