




Product Number: 322-LFS-DS/04

Combination Screw - Solder Terminal Strips for Panel / Chassis Mounting

Type: 322-LFS (-DS)



Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing - 3.5 mm

When locating connector, allow 0.5 mm clearance around it for process-induced variations.

Description

LFS Types feature sturdier solder tabs for connection up to 10 AWG.

- Standard version
- Rigid solder tab
- Recommended mounting hardware: M3.5 pan head screw (#6-32 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.

Technical Data

Center to Center Spacing: 10 mm (0.394 in.)
Nominal Cross Section: 2.5 mm² (3874 mils²)
Wire Stripping Length: 7 mm (0.28 in.)