


Flexible Coaxial Cable Assembly

114-2626-xxxxA



List Nomenclature

- | | |
|--------------------------------------|------------------|
| 1. BNC straight plug brass connector | A04050 |
| 2. Black Protective sleeve | A20008 |
| 3. Identification Marking | |
| 4. Coaxial Cable | A90043 (RG59B/U) |

Electrical Specifications

Impedance	:	75 ± 2 Ohms
Operating Frequency	:	DC to 1 GHz
Velocity of Propagation	:	66%
Voltage Withstand	:	1000 Veff

Insertions Losses

Frequency (MHz)	10	50	100	500	1000
Insertions Losses max (dB/m)	0,05	0,10	0,15	0,30	0,48

Mechanical Specifications

Cable Diameter	Ø 6,15 mm (0,24 inches)
Static Bend radius	Ø 50,0 mm (2 inches)
Connector Tensile Force	400N min

Environmental Specifications

Operating Temperature Range	:	-40°C à +80°C
Sealing	:	Runoff

Conditions of delivery

Mechanical check	:	Length
Electrical test	:	Continuity / Rigidity