

C-Series





The C-Series toggle switches are single pole switches with ratings up to 20 amps and 1 1/2 horsepower. These switches are available with plated brass toggles and bushings.

- Specifications
- Certifications\*: UL, CSA
  - Dielectric Strength: 1,000V (minimum)
  - Insulation Resistance: 100 Megohms (minimum)
  - Base Material: Polyarylether
  - Actuator Material: Brass/Nickel Plate
  - Bushing Material: Brass/Nickel Plate

\* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



SERIES

C

CIRCUIT

A

RATING

20

TERMINATION

1

TOGGLE STYLE

73

C SINGLE POLE TOGGLE	A ON-NONE-OFF B ON-NONE-ON	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC 20 10A 250VAC 20A 125VAC 1 1/2HP 125-250VAC	0 SOLDER LUG 1 .250TAB (QC) 4 SCREW TERMINAL 5 WIRE LEAD	TOGGLE BUSHING SUFFIX NEOPRENE LENGTH LENGTH NO. SEAL .406 .343 52 57 .687 .465 73 78
----------------------	-------------------------------	---	---	--

NOTES:  
Shading indicates standard configurations.