

Heavy Duty Power Cord, 16A (IEC309 to C19) 10-ft.

MODEL NUMBER: **P070-010**



Highlights

- 10ft IEC309 (2P+G) to C19 Power Cord
- 16A, 250V rated
- RoHS Compliant

Package Includes

- 10ft, IEC 309 to C19 Power Cord

Description

10ft, IEC 309 (2P+ Ground) to C19 power cable. 16 Amp, 90 - 250 VAC range. RoHS compliant.

Features

- 10ft IEC 309 to C19 Power cord
- 16A, 250V rated
- H05VV-F 1.5mm² x 3G Cable

Specifications

OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332160706
PHYSICAL	
Color	Black

CONNECTIONS	
Connector A	 BLUE IEC-309 16A 2P+E
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.