


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NO.* | MAT'L<br>SUFFIX          | RECOMMENDED<br>FASTENER | 'A'               | 'B'               | 'C'              | 'D'                                  | 'E'                                  | 'F'              | 'G'<br>'REF'     | 'H'<br>'REF' | 'J'<br>'REF' | USE WITH<br>THESE CABLE<br>TIE CROSS<br>SECTIONS   | WEIGHT (g)<br>lbs/100<br>pcs. |
|----------------------|--------------------------|-------------------------|-------------------|-------------------|------------------|--------------------------------------|--------------------------------------|------------------|------------------|--------------|--------------|----------------------------------------------------|-------------------------------|
| TM3S8                | NONE<br>-0<br>-30<br>-49 | #8 (M4)<br>SCREW        | 0.863<br>[ 21.9 ] | 0.610<br>[ 15.5 ] | 0.373<br>[ 9.4 ] | 0.320<br>[ 8.1 ]<br>±.020<br>[ 0.5 ] | 0.088<br>[ 2.2 ]<br>±.020<br>[ 0.5 ] | 0.208<br>[ 5.3 ] | 0.105<br>[ 2.7 ] | 0.325        | 0.180        | MINIATURE<br>INTERMEDIATE<br>STANDARD<br>LT. HEAVY | 0.369<br>[ 167.5 ]            |
| TM3S10               | NONE<br>-0<br>-30        | #10 (M5)<br>SCREW       |                   |                   |                  |                                      |                                      |                  | 0.115<br>[ 2.9 ] | 0.385        | 0.200        |                                                    | 0.363<br>[ 165.0 ]            |
| TM3S25               | NONE<br>-0<br>-30        | 1/4" (M6)<br>SCREW      | 0.879<br>[ 22.3 ] | 0.629<br>[ 16.0 ] | 0.379<br>[ 9.6 ] |                                      |                                      | 0.210<br>[ 5.3 ] | 0.155<br>[ 3.9 ] | 0.506        | 0.262        |                                                    | 0.296<br>[ 134.5 ]            |
| TM3S2510             | -30<br>-39               | #10 (M5)<br>SCREW       | 0.873<br>[ 22.2 ] | 0.620<br>[ 15.7 ] |                  |                                      |                                      | 0.212<br>[ 5.4 ] | 0.120<br>[ 3.0 ] | 0.480        | 0.200        |                                                    | 0.321<br>[ 145.5 ]            |


NOTES:

- \*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.


| MAT'L<br>SUFFIX | MATERIAL                | COLOR   |
|-----------------|-------------------------|---------|
| NONE            | NYLON 6/6               | NATURAL |
| -0              | WEATHER RESISTANT NYLON | BLACK   |
| -30             | HEAT STABILIZED NYLON   |         |
| -39             | HEAT STABILIZED NYLON   | NATURAL |
| -49             | IMPACT MODIFIED NYLON   |         |



SEE NOTE 2



SECTION A - A



|                                                                                                                                           |                                                                                                  |
|-------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|
| DIMENSIONS IN BRACKETS ARE METRIC [ mm ]                                                                                                  |                                                                                                  |
| CAD FILENAME/LAYERS G00239EN_PB_TM3S_11                                                                                                   |                                                                                                  |
| <b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS                                                                                                |                                                                                                  |
| TM3S - TIE MOUNT                                                                                                                          |                                                                                                  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ±0.05 [ 1.3 ] (.XXX) ±0.010 [ 0.25 ]<br>(.XX) ±0.02 [ 0.5 ] ANGLES ±5° | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE<br>PROJECTION. |
| DRAWN BY<br>AJV                                                                                                                           | MAT'L:<br>SEE TABLE                                                                              |
| DATE<br>12/17/96                                                                                                                          | SCALE<br>NONE                                                                                    |
| CHK'D                                                                                                                                     | DWG<br>GB0239EN<br>SIZE<br>A                                                                     |

| REV | DATE     | BY   | CHK | DESCRIPTION                                                     | ECN      | R  | CUST | SUP |
|-----|----------|------|-----|-----------------------------------------------------------------|----------|----|------|-----|
| 11  | 4/16/07  | DJSM |     | ADDED DECIMAL PLACE TO TABLE,<br>REMOVED MATERIALS -69 AND -100 | GB0239EN | 11 |      |     |
| 10  | 03/19/07 | DJSM |     | ADDED TM3S2510, ADDED MATERIAL<br>-39, CHANGED TOLERANCES       | GB0239EN | 10 |      |     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[TM3S25-C0](#) [TM3S10-M30](#) [TM3S25-M0](#)