


KEMET, FLLD4-TH, EMI Filters, Three Phase, 530 VAC, 16 A, 120x115x80mm



Dimensions	
L	120mm NOM
W	115mm NOM
H	80mm NOM
L1	80mm NOM
W1	127.5mm NOM
W2	143mm NOM
J	32mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6

General Information	
Series:	FLLD4-TH
Style:	Chassis Mount
Description:	EMI Filter, Classis Mount, Compact
Features:	High Performance
RoHS:	Yes
Qualifications:	IEC/EN 60939, UL 1283

Specifications	
Voltage AC:	530/305 VAC
Rated Frequency:	50-60 Hz
Current:	16 A (50C)
Rated Temperature:	50C
Temperature Range:	-25/+100C
Climate Category:	25/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	6 W (25C 50 Hz)
Leakage Current:	11 mA

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	800 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.