


LOW PROFILE SMD & DIP TRANSFORMERS



For DC/DC Converters

FEATURES


- Designed for isolation and voltage outputs in DC/DC converter circuits.
- Standard 6 pin SMD or DIP packages.
- Efficient toroidal design with excellent EMI suppression.
- Low cost.




PACKAGE - SMD



PACKAGE - DIP



SCHEMATIC



Drawing NOT to scale. Dimensions Inches/mm +/- 0.01" Unless noted

ELECTRICAL CHARACTERISTICS @ 25°C

Part Number		OCL	Turns Ratio		Insulation Resistance	ET Constant	Dissipation Rating	DCR Pri/Sec	Dielectric Test
		uH	Ratio		MOhms	V-uS	mW	Ohmn	Vrms
SMD	DIP	NOM	PRI	SEC	MIN	MIN	MAX	MAX	MIN
26Z291	14Z3231	1500	2CT:1CT		10,000	16	300	0.80/0.30	2000
26Z292	14Z3232	1500	8CT:3CT		10,000	16	300	0.80/0.30	2000
26Z293	14Z3233	1500	4CT:3CT		10,000	16	300	0.80/0.60	2000
26Z294	14Z3234	1500	3CT:4CT		10,000	16	300	0.80/0.90	2000