

**General ordering data**

Order No.	7904180000
Part designation	ZDU 4/3AN
Version	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
EAN	4008190575953
Qty.	50 pc(s).

Product notes

Note, technical data	When using twin ferrules, the rated voltage is 690 V.
Product description	Z-series standard ranges provide solutions for conductor cross-sections from 0.05 to 35 mm ² .

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA00ATEX2107U
Download, German	KEMA00ATEX2107U_d.pdf
Download English	KEMA00ATEX2107U_e.pdf
IECEX Certificate of Conformity	IECEXULD05.0009U
ATEX voltage	550 V
ATEX current	28 A
ATEX conductor cross-section	4 mm ²
IECEX voltage	550 V
IECEX current	28 A
IECEX conductor cross-section	4 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEX-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	dark beige
Connection direction	top

Additional technical data

End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	3
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Clamped
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	35 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 10

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	top
No. of connections	3
Stripping length	12 mm
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A4
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Stranded, min.	0.5 mm ²
Stranded, max.	6 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	6 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	4 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	1.5 mm ²

Conductors for clamping (rated connection)

AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	5.26 mm ²

Dimensions

Width	6.1 mm
Height of lowest version	43.5 mm
Length	83.5 mm
TS 35 offset	50.5 mm

Rating data

Rated cross-section	4 mm ²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	32 A
Standards	IEC 60947-7-1
Current with max. conductor	41 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	33 A
Min. cross-section (UL)	AWG 26
Max. cross-section (UL)	AWG 10

Approvals

Approvals institutes

**Downloads**

STEP	7904180000_28611_ZDU_4-3AN_STP.stp
------	------------------------------------

Classifications

eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
1632050000	ZDU 4	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1632060000	ZDU 4 BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35
1683590000	ZDU 4 GE	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, yellow, TS 35
1683630000	ZDU 4 GR	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, grey, TS 35
1636830000	ZDU 4 OR	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, Orange, TS 35
1683580000	ZDU 4 RT	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, red, TS 35
1683650000	ZDU 4 SW	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, black, TS 35
1683640000	ZDU 4 WS	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, white, TS 35
1651900000	ZDU 4/10/BEZ	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
7904190000	ZDU 4/3AN BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35
7904290000	ZDU 4/4AN	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
7904300000	ZDU 4/4AN BL	Feed-through terminal, 4 mm ² , Tension clamp connection, Wemid, blue, TS 35