

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301100026](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Pro-Yellow 20W Halogen Magnet Mount Machine Light, with Molded 18-/Cord Type, SJTO Overall Cord Length 3.04m (10.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
Series [130110](#)  
NEMA Configuration NEMA 5-15  
NEMA Rating Rain Tight  
Outlet None  
Overview [Wide-Area Lighting Products](#)  
Product Name Pro-Yellow  
Type Wide Area Lamps  
UPC 78678808541

**Physical**

Cord Length - Primary 3.04m (10.0')  
Cord Length - Secondary N/A  
Depth 118.11mm (4.650")  
Duty General  
Guard Included No  
Guard Type N/A  
Height 89.92mm (3.540")  
Length 549.91mm (21.650")  
Material - Globe Tempered Glass  
Material - Guard Nylon  
Mounting Style Magnet  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Quartz Halogen  
Cord Type - Primary 18/3 SJTO  
Lamp Type N/A  
Lamp Wattage - Maximum 20W  
Lumens 500  
On/Off Switch Yes  
Voltage (Fixture) - Maximum 120V AC

**Material Info**

Engineering Number 8540M



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Relevant |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130110](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION