

HELAGRIP Mk2 INTERLOCKING CABLE MARKERS

A range of five sizes of soft PVC chevron-shaped markers which will fit BS 6004 cable sizes between 0.5mm² and 70mm².

- White with black marking*
- Available semi-severed on shrink wrapped self-grip reels or fully severed in bags (according to size).
- Right facing chevron makes markers compatible with other makes.
- Soft PVC and profile design ensures easy fitting without tools.
- Temperature range: -65°C to +70°C.
- CEEB approved.
- Markings available A-Z, 0-9, +, -, /.
- ≡ and Blank to special order.
- Reels colour coded according to marker size, viz: Ref 00- Grey. Ref 1-3 Blue. Ref 2-5 Green. Ref 4-7 Yellow. Ref 4-9 Red.

SIZES AVAILABLE

CABLE SIZE BS 6004 MM ²	INSULATION O.D. MM	MARKER REF	MARKER LENGTH MM
0.5 - 0.75	1.27 - 2.0	00	3
0.75 - 1.0	1.3 - 2.8	1-3	3
1.0 - 4.0	2.25 - 5.0	2-5	4
2.5 - 6.0	3.5 - 6.5	4-7	5
2.5 - 16	4.0 - 9.0	4-9	5
16 - 70	8.0 - 16.0	8-16	6

N.B. Ref 00 markers available semi-severed only in a full range of markings.

Ref 1-3, 2-5, 4-9 markers available semi-severed in a full range of markings but available fully severed to special order with markings 0-9 only.

Ref 8-16 markers available fully severed only in a full range of markings.

*Colour coded markers are available in sizes 1-3 and 2-5 only with marking 0-9 (reel packed only).

Straight-cut non-interlocking markers are also available to special order.



Order Coding example

HGRN00 (0-9) P801 - P810
HGRN00 (A-N) P831 - P844
HGRN00 (P-Z) P845 - P856
HGRN00 (+, -, /) P857 - P859

276-509

To

276-893



SEMI-SEVERED MARKERS

Packed on reels to facilitate storage, handling and application. Each reel is individually shrink wrapped.

BLACK ON WHITE

SIZE	REF	ORDER CODE	MARKERS PER REEL
00	HGRN 00	P801 - 59	1000
1-3	HGRN 1-3	P2001 - 59	1000
2-5	HGRN 2-5	P2101 - 59	500
4-7	HGRN 4-7	P2801 - 59	500
4-9	HGRN 4-9	P2201 - 59	250

COLOUR CODED

SIZE	REF	ORDER CODE	MARKERS PER REEL
1-3	HGRNCC 1-3	P2301 - 10	1000
2-5	HGRNCC 2-5	P2311 - 20	500

FULLY SEVERED MARKERS

Markers are packed in sealed polythene bags and boxed in quantities as detailed below.

SIZE	REF	ORDER CODE	MARKERS PER BAG	MARKERS PER BOX
8-16	HGN 8-16	P2701 - 59	250	250

HELVIN CABLE MARKERS GENERAL PURPOSE PVC


As identification sleeves they provide a really permanent means of identifying cables. Each product consists of 500 separate markers or 5 x 100 strips in case of unicut. Standard lengths as in tables opposite. Temperature range -65°C to $+70^{\circ}\text{C}$. Comply with BS 3858 Type 3.

CEGB TYPE APPROVAL No. 112

ALL SIZES ARE COLOUR CODED
0-9 - Black, Brown, Red, Orange, Yellow, Green, Blue, Violet, Grey, White.

A-Z - Available Black on Yellow to special order.

Minimum quantity, 1000 of each.



Unicut sleeves are produced by a special process to facilitate easy 'picking off'.

FULLY SEVERED 0-9 COLOUR CODED

ORDER CODE	REF	INTERNAL DIA. MM	LENGTH MM	MAX. O.D. OF CABLE MM
P3121-30	P20	2.0	5.0	3.0
P3161-70	P25	2.5	5.0	3.7
P3201-10	P30	3.0	5.0	4.4
P3241-50	P40	4.0	5.0	5.9
P3281-90	P55	5.0	5.0	8.2

SEMI SEVERED 0-9 COLOUR CODED

ORDER CODE	REF	INTERNAL DIA. MM	LENGTH MM	MAX. O.D. OF CABLE MM
P3441-50	PU10	1.0	3.0	1.5
P3481-90	PU12	1.2	3.0	1.8
P3521-30	PU15	1.5	3.0	2.2
P3561-70	PU20	2.0	5.0	3.0
P3601-10	PU25	2.5	5.0	3.7
P3641-50	PU30	3.0	5.0	4.4

OVALGRIP CABLE MARKERS

A range of sleeves and cable markers in Helvin grade P.V.C. for fitting without the aid of tools.


Ovalgrip are oval in shape and are fitted by pressing into a circular shape then sliding over the cable end or terminal, and releasing.

Temperature range -65°C to $+70^{\circ}\text{C}$.

CEGB TYPE APPROVAL No. 112

ALL SIZES ARE COLOUR CODED
0-9 - Black, Brown, Red, Orange, Yellow, Green, Blue, Violet, Grey, White.

0-9, A-Z - Available Black on White, in two sizes only HO50, HO85 (suitable for use on Arrowtags), packed in bags of 100.



COLOUR CODED

ORDER CODE	REF	INTERNAL DIA. (A) MM	INTERNAL DIA. (B) MM	MAX. O.D. OF CABLE MM	STANDARD WALL THICKNESS
P381-90	H030	3.09	0.89	2.16	0.58
P421-30	H040	3.83	1.12	2.67	0.66
P461-70	H050	5.30	1.52	3.68	0.84
P541-50	H085	8.58	2.48	5.97	0.96

Standard length 5mm

BLACK ON WHITE

ORDER CODE	REF	INTERNAL DIA. (A) MM	INTERNAL DIA. (B) MM	MAX. O.D. OF CABLE MM	STANDARD WALL THICKNESS
P101-P156	H050	5.30	1.52	3.68	0.84
P201-P256	H085	8.58	2.48	5.97	0.84