

Data Sheet

20MHz DDS Sweep Function Generator with Arb Function

Model 4045

The model 4045 DDS Function Generator is a must-have for anyone needing a low cost, full featured direct digital synthesis (DDS) function generator with arbitrary waveform capabilities. The 4045 has a menu-driven front panel interface that includes a large, easy-to-read graphical LCD display. Waveform parameter changes and data entry can be made using the rotary knob or via the built-in USB interface. The unit generates superb quality waveforms with high signal precision and stability. It provides sine & square wave outputs over the frequency range from 0.1 Hz to 20 MHz in one extended range (triangle/ramped wave outputs to 2MHz). Arbitrary waveforms can be edited from scratch or by modifying standard waveforms. A full range of triggering capabilities is available, including internal-external trigger source, gated and burst modes of operation.

- 20MHz Frequency Range (sine & square only)
- Sine, Square & Triangle waveforms
- Arbitrary waveforms to 1,000 points
- Clean, precise DDS waveform generation
- Modulation in both AM & FM
- Lin or Log Sweep Function
- Adjustable Duty Cycle
- Adjustable DC Offset
- Bright informative LCD
- USB Interface
- Free downloadable software



Graphical LCD display



USB connection

Model	4045
Frequency Range	0.1Hz to 20MHz (sine & square wave only)
Waveforms	Sine, Square, Triangle, Arbitrary, Ramp, Pulse
Amplitude	10V p-p into 50Ω
Attenuation	-20dB + 1dB
Offset	± 4.5V into 50 Ω (amplitude dependent)
Distortion (for sine wave at 5 Vp-p into 50 Ω)	DC-20KHz = -55 dBc
Square Rise/Fall Time	<18 ns (10% to 90%) into 50 Ω
Flatness (for sine wave at 5 Vp-p into 50 Ω)	0.5 dB at 1MHz (1 dB to 20 MHz)
Power Source	90V-264V, 48-66Hz / 30 VA max
Dimensions (WxHxD)	8.4 x 3.5 x 8.3" (213 x 88 x 210 mm)
Weight	5.5 lbs, 2.5 Kg (approx.)
Three Year Warranty	
Included Accessories	Manual, software CD, USB cable, power cord, test report and certificate of calibration

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[4045-NIST](#)