


REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT
B	07/17/07	REVISE OVERALL LENGTH, BACK END CONFIGURATION



8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7					DRAWN	G.R.S.						07/17/07
6					CHECKED			PART DESCRIPTION SMA PLUG TO MMCX JACK				
5	GASKET	SILICONE	RED		1	ISSUED						
4	RETAINER RING	BER. COPPER	GOLD		1	SHEET	1 OF 1					
3	CONTACT PIN	BER. COPPER	GOLD		1			PART NO. 242140				
2	INSULATOR	TEFLON	NATURAL		1							
1	BODY	BRASS	GOLD	1			DWG. NO. 242140.DWG REV. B SIZE A SCALE NA					
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/242/242140.DWG							