



NYS373-*

Phono plug, black shell, gold plated contacts, rubber boot for best antikink protection, chuck type strain relief for cable O.D. 3.5 to 6.1 mm, color coding ring

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White



Image gallery



Technical Information [hide](#)

Product	
Title	NYS373-*
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
Mechanical	
Cable O.D.	3.5 - 6.1 mm
Lifetime	> 1000 mating cycles
Wiresize	24 AWG
Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)

Shell plating	Black
Strain relief	Internal plastic chuck
Insulation	Thermoplastic
Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN
REAN a brand of Neutrik AG